



## 265.SR - Non sparking chisels



### Description:

- Special non sparking and anti-magnetic Copper-Beryllium alloy.



	A [mm]	Length L [mm]	Length L1 [mm]	Weight [g]
<b>263.30SR</b>	25.0	300.0	28.0	1200.0
<b>263.32SR</b>	30.0	300.0	35.0	2900.0
<b>265.20SR</b>	10.0	150.0	12.0	100.0
<b>265.22SR</b>	12.0	160.0	14.0	240.0
<b>265.24SR</b>	14.0	200.0	16.0	250.0
<b>265.26SR</b>	16.0	160.0	18.0	260.0
<b>265.28SR</b>	17.0	350.0	19.0	900.0
<b>265.29SR</b>	22.0	600.0	24.0	1800.0