

1

2

3

4


5

6

7

| | | | |
|-----------|---------------------|-------------|------|
| Signature | Revision History | Date | Rev. |
| Sean | For Bulk Production | May.20,2013 | 01 |

RoHS Compliant



NOTES:

1.CABLE: NO-UL 30AWG(7/0.09BC)*4C+PVC JACKET OD=3.5±015mm JACKET COLOR: BLACK

2.CONNECTOR:

P1 : USB A/M, SOLDER, WHITE INSULATION, GOLD FLASH PLATED CONTACTS, NICKEL PLATED SHELL
P2 : USB A/F, SOLDER, WHITE INSULATION, GOLD FLASH PLATED CONTACTS, NICKEL PLATED SHELL


3.HOOD: MOLDED TYPE,PVC 45P,COLOR:BLACK

4.ELECTRICLE TEST:

- (1)100% OPEN SHORT & MIS WIRE TEST.
- (2)CONTACT RESISTANCE 3 ohm Max .
- (3)INSULATION RESISTANCE 5M ohm Min .
- (4)HI-POT TEST:DC 300V/10ms

| PIN ASSIGNMENT | | | |
|----------------|-------|----|--------|
| P1 | | P2 | |
| 1 | RED | 1 | VCC |
| 2 | GREEN | 2 | -DATA |
| 3 | WHITE | 3 | +DATA |
| 4 | BLACK | 4 | GROUND |

Cross Section:



| | | | | | |
|-------------|--|---------------------|------|-------------------|--|
| | | Date | Name | Part No. | |
| Drawn by | | May.20,2013 | Sean | AK-300200-018-S | |
| Checked by | | May.20,2013 | Joe | EAN:4016032283102 | |
| Approved by | | May.20,2013 | Andy | Title | |
| | | USB A/M - A/F CABLE | | | |
| | | Scale | N/A | Sheet | |
| | | Unit | MM | 1/2 | |

ASSMANN Electronic GmbH

STxxxxx

1

2

3

4

5

6

7

Package Details

RoHS Compliant


| | | | |
|-----------|---------------------|-------------|------|
| Signature | Revision History | Date | Rev. |
| Sean | For Bulk Production | May.20,2013 | 01 |

Single Cable

| P/N | Cable Length | Rolling Size (Single Cable) | Polybag Type (Single Cable) | Bag Size (Single Cable) | Article Weight (Single Cable) |
|-----------------|--------------|-----------------------------|--------------------------------|-------------------------|-------------------------------|
| AK-300200-018-S | 1.8m | mm max. | Ordinary Polybag (Heat Sealed) | *0.03mm | kg |

Inner Packing Unit

| P/N | Cable Length | Quantity (Inner Packing Unit) | Type (Inner Packing Unit) | Size (Inner Packing Unit) | Weight (Inner Packing Unit) |
|-----------------|--------------|-------------------------------|---------------------------|---------------------------|-----------------------------|
| AK-300200-018-S | 1.8m | 10 pcs | Polybag (Heat Sealed) | *0.03mm | kg |




Inner Packing Unit



CARTON DETAILS

| P/N | Cable Length | Quantity (Carton) | Measurement (Carton) | N.W. (Carton) | G.W. (Carton) |
|-----------------|--------------|-------------------|----------------------|---------------|---------------|
| AK-300200-018-S | 1.8m | pcs | cm | kg | kg |



* "ROTTERDAM" is for Sea Freight shipment
 * "COLOGNE" is for Air Freight shipment
 * "LUDENSCHIED" is for Fedex or UPS shipment

| | | | |
|-----------------------------------|-------------|-------|------------------------|
| | Date | Name | Part No. |
| Drawn by | May.20,2013 | Sean | AK-300200-018-S |
| Checked by | May.20,2013 | Joe | EAN:4016032283102 |
| Approved by | May.20,2013 | Andy | |
| ASSMANN Electronic GmbH | | | Title |
| | | | USB A/M - A/F CABLE |
| Scale | N/A | Sheet | 2/2 |
| Unit | MM | | |

STxxxxx