


APPLICATIONS: EIA rack-mount chassis, industrial work stations, data processing, mechanical devices, medical applications, tool boxes, and point-of-purchase displays. **This product is covered by U.S. and various foreign patents issued and/or pending.**

MODEL 204-ALR

Up to 140 lb. [64 kg.] Capacity*



- Finish Bright electro-zinc plating (C) or black zinc (CB)**
- Length 12" 28" [305mm 711mm]
- Travel 3/4 length of slide
- Height 1.38" [35.1mm]
- Sidespace .38" [9.6mm]

- Mounting Side, bracket or hard mounting
- Movement Steel ball bearing
- Hardware #8 pan head screw
- Features Positive lock-out with front disconnect, Positive rear stop

**Minimum order quantities may apply.


*Load rating based on a 16" wide drawer cycled 10,000 times.

Part Number	Slide Length	Slide Travel	Load Rating * lbs. / [kg]	Α	В	С	D	Е	F	G
204-A12-LR	12.00 [305]	8.00 [203]	140 [64]		8.50 [215.9]	10.00 [254.0]		5.87 [149.1]	10.25 [260.4]	10.75 [273.1]
204-A14-LR	14.00 [356]	10.00 [254]	130 [59]		10.50 [266.7]	12.00 [304.8]		7.87 [199.9]	12.25 [311.2]	12.75 [323.9]
204-A16-LR	16.00 [406]	12.00 [305]	120 [55]		12.50 [317.5]	14.00 [355.6]		9.87 [250.7]	14.25 [362.0]	14.75 [374.7]
204-A18-LR	18.00	13.00	110	8.00	13.50	16.00	8.37	11.87	16.25	16.75
	[457]	[330]	[50]	[203.2]	[342.9]	[406.4]	[212.6]	[301.5]	[412.8]	[425.5]
204-A20-LR	20.00	15.00	92	9.00	15.50	18.00	9.37	13.87	18.25	18.75
	[508]	[381]	[42]	[228.6]	[393.7]	[457.2]	[238.0]	[352.3]	[463.6]	[476.3]
204-A22-LR	22.00	16.00	85	10.00	16.50	20.00	10.37	15.87	20.25	20.75
	[559]	[406]	[39]	[254.0]	[419.1]	[508.0]	[263.4]	[403.1]	[514.4]	[527.1]
204-A24-LR	24.00	17.00	78	11.00	17.50	22.00	11.37	17.87	22.25	22.75
	[610]	[432]	[35]	[279.4]	[444.5]	[558.8]	[288.8]	[453.9]	[565.2]	[577.9]
204-A26-LR	26.00	19.00	70	12.00	19.50	24.00	12.37	19.87	24.25	24.75
	[660]	[483]	[32]	[304.8]	[495.3]	[609.6]	[314.2]	[504.7]	[616.0]	[628.7]
204-A28-LR	28.00	20.00	60	13.00	20.50	26.00	13.37	21.87	26.25	26.75
	[711]	[508]	[27]	[330.2]	[520.7]	[660.4]	[339.6]	[555.5]	[666.8]	[679.5]

Installation Instructions

Instructions to Bracket Mount

- 1. To ensure proper operation of the slides, make certain that all bracket mounting screws are inserted so that the screw heads are inside the slides. (No washers on the inside of the slides.)
- 2. Separate slide members by depressing the lock release lever.
- 3. Using mounting kits and brackets, mount brackets to slide cabinet members (largest). For adjustment purposes screw the back brackets on loosely.
- 4. Install slides into EIA rack with #10-32 screws (customer supplied) and secure with bar nuts. Rear adjustment is possible by aligning the back bracket. Do not tighten screws until final adjustment is made.
- 5. Mount slide drawer members (smallest) to the chassis. Position slides 1/8" from the front edge of the chassis making sure both slides are parallel.
- 6. With cabinet member ball retainers fully forward, install chassis by engaging the slide members and close completely. Check slide alignment by opening and closing the chassis. Any sign of binding indicates lateral stress or misalignment.
- 7. Adjust slide position until movement is smooth. Tighten all screws and if necessary use more screws to secure slides and complete installation.



Instructions to Hard Mount

- 1. Follow steps 1 & 2 of "Bracket Mount" instructions.
- 2. Install slide cabinet members (largest) into cabinet using #8 pan head screws. Be sure slides are parallel.
- 3. Mount slide drawer members (smallest) onto chassis. Leave all screws loose for future adjustment. Make sure slides are parallel.
- 4. Follow steps 6 & 7 of "Bracket Mount" instructions.

Slide Ordering Instructions

Complete your slide order for model 204-ALR by specifying the following: 40 D · 0 004 440 1 0 0

	<u>10 Pair</u>	<u>C 204 -A18-L</u>	<u>R D</u>
Total Slides Required ———			
Slide Finish			
Slide Model ———			
Slide Length ————			
Intional Dalukaa Daakaaina (ina	ludoo mou	unting corowa)	

Optional Polybag Packaging (includes mounting screws) —

Packaging

Distributor (D) Pack: All lengths are packaged 10 pair per box. Polybag includes one pair of slides packed with screws.

Bulk (P) Pack:	Lengths 12'	' - 16"	50 each per box
	Length 18	II	40 each per box
	Lengths 20	" - 22"	30 each per box
	Lengths 24	-" - 28"	20 each per box

Order optional bracket mounting hardware kit (part number 4180-0222-XE) separately.


Optional Hardware Kit - Ordered Separately

Kit contains 4 each short mounting brackets and mounting hardware. Order 1 kit per pair of slides.

10 Each 4180-0222-XE Optional Bracket Kit Part Number

Bracket kit includes the following. See Figure 1.

(Part number 4000-0180-CE) 4 short brackets 1 bracket hardware kit* (Part number 4180-0230-XE) (*Kit contains screws, hex-nuts, washers, bar nuts)



Specifications

Total Bracket Kit Required -

Slide members: Cold rolled steel Ball retainers: Cold rolled steel Ball bearings: Carburized steel

Note: Specifications, materials, prices, terms, and delivery are subject to change without notice.



ACCURIDE INTERNATIONAL INC. 12311 Shoemaker Avenue Santa Fe Springs, CA 90670 TEL (562) 903-0200 FAX (562) 903-0208 www.accuride.com Manufacturing, Engineering, and Sales United States • Germany • Japan • Mexico • United Kingdom