



Technical Data Sheet:	DS561/0812
Product Description	90 degree elbow, external thread, nickel plated brass, FSU, FNU and LFHU conduit fitting.
Product Range	FSU - C90 Type fitting (Metric threads)

Roman Way, Coleshill
Birmingham
B46 1HG, United Kingdom
Tel: 00 44 (0)1675 466900
Website: www.flexicon.uk.com



Material: Nickel Plated Brass
Colour: Self colour
Fire Performance: Inherently Low Fire Hazard
IP Rating: • IP65
Applications: Nickel plated brass compression fitting comprising of nut, earthing ferrule and nylon compression seal. The earthing ferrule is manufactured in machined nickel plated brass to facilitate easy assembly and re-use. Also ensures high mechanical strength and electrical continuity.
Features: • High tensile strength • Oil resistant • UV resistant • Corrosion resistant • Conforms to EN 61386
Temperature Performance: -50°C to +135°C

Conduit Size	Part No.	Metric Thread	Nominal Dimension (mm)				
			A	B	C	D (A/F)	E
12	FSU12-M16-C90	M16 X 1.5	10.0	17.5	22.0	8.6	20.0
16	FSU16-M16-C90	M16 X 1.5	10.0	17.5	26.0	11.5	20.0
16	FSU16-M20-C90	M20 X 1.5	13.0	20.0	26.0	11.5	24.0
20	FSU20-M20-C90	M20 X 1.5	13.0	20.0	29.0	15.3	24.0
25	FSU25-M25-C90	M25 X 1.5	14.0	25.3	35.0	19.1	30.0
32	FSU32-M32-C90	M32 X 1.5	15.0	31.0	42.0	26.0	36.0

Compliance, Approvals & Accreditation;



EN 61386 Classification Available on request
COMPLIANT TO LUL STANDARD 1-085-A3
London Underground Certificate No. 296

Typical Applications;



Errors, omissions and amendments excepted. As part of continuing product development Flexicon Ltd reserve the right to alter product specifications without prior notice. Data given is correct at time of compilation. Product specification and application data is for guidance only and does not constitute a warranty of any kind, either expressed or implied for Flexicon products or their suitability for a specific purpose. Third party approvals maybe limited to certain sizes within a product range.