

## 82H - Short metric keys




### Standards:

NF ISO 2936, ISO 2936, DIN ISO 2936, ASME B18.3.2M

### Description:

- Manufactured in silicon steel.
- Finish: phosphate-coated.



	A [mm]	Length L [mm]	Height H [mm]	Weight [g]
<b>82H.0.9</b>	0.9	38.0	12.0	0.3
<b>82H.1.3</b>	1.3	45.0	13.0	0.7
<b>82H.1.5</b>	1.5	38.0	13.0	5.0
<b>82H.10</b>	10.0	112.0	40.0	100.0
<b>82H.11</b>	11.0	118.0	42.0	130.0
<b>82H.12</b>	12.0	125.0	45.0	165.0
<b>82H.13</b>	13.0	135.0	50.0	205.0
<b>82H.14</b>	14.0	140.0	55.0	260.0
<b>82H.15</b>	15.0	150.0	58.0	310.0
<b>82H.16</b>	16.0	154.0	60.0	370.0
<b>82H.17</b>	17.0	160.0	63.0	440.0
<b>82H.18</b>	18.0	170.0	66.0	540.0
<b>82H.19</b>	19.0	180.0	70.0	640.0
<b>82H.2</b>	2.0	50.0	16.0	2.0
<b>82H.2.5</b>	2.5	62.0	17.0	3.0
<b>82H.22</b>	22.0	200.0	80.0	950.0
<b>82H.23</b>	23.0	210.0	85.0	1100.0
<b>82H.24</b>	24.0	224.0	90.0	1300.0
<b>82H.27</b>	27.0	250.0	100.0	1300.0
<b>82H.3</b>	3.0	65.0	20.0	5.0
<b>82H.3.5</b>	3.5	66.0	22.0	8.0
<b>82H.32</b>	32.0	315.0	125.0	1400.0
<b>82H.4</b>	4.0	70.0	25.0	10.0
<b>82H.4.5</b>	4.5	75.0	26.0	15.0
<b>82H.5</b>	5.0	80.0	28.0	20.0
<b>82H.6</b>	6.0	90.0	32.0	30.0
<b>82H.7</b>	7.0	95.0	34.0	45.0
<b>82H.8</b>	8.0	100.0	36.0	60.0

**82H.9**

9.0

105.0

38.0

80.0