


# electrical connection box

## VAVE-L1-1VL1-LP

Part number: 566722

FESTO



### Data sheet

Feature	Value
Polarity protected	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V 24 V
Surge strength	0.8 kV
Degree of contamination	3
Extended ambient temperature	-5 - 60 °C
Corrosion resistance classification CRC	0 - No corrosion stress
Protection class	IP40
Ambient temperature	-5 ... 50 °C
Assembly position	Any
Product weight	4.6 g
Terminal cross-section	0.14 mm <sup>2</sup>
Electrical connection	Stranded wire
Cable length	0.5 m
Protective earth connection	Not available
Mounting type	Clip
Housing colour	Black
Materials note	Conforms to RoHS
Material housing	PA