



Dimensions in mm.

W5 Partno.	No pos	Length	With
CLL-3309-A	4	100	7,6
CLL-3309-A1	4	150	7,6
CLL-3309-A2	4	250	7,6
CLL-3309-B	6	100	10,1
CLL-3309-B1	6	150	10,1
CLL-3309-B2	6	250	10,1
CLL-3309-C1	8	150	12,7
CLL-3309-C2	8	250	12,7
CLL-3309-D	10	100	15,2
CLL-3309-D1	10	150	15,2
CLL-3309-D2	10	250	15,2
CLL-3309-E1	12	150	17,8
CLL-3309-F	14	100	20,3
CLL-3309-F1	14	150	20,3
CLL-3309-F2	14	250	20,3
CLL-3309-G05	16	50	22,8
CLL-3309-G	16	100	22,8
CLL-3309-G2	16	250	22,8
CLL-3309-H1	18	150	25,4
CLL-3309-I	20	100	27,9
CLL-3309-I1	20	150	27,9
CLL-3309-I2	20	250	27,9

Cable details: Flat ribbon cable grey  
28 AWG 1,27mm pitch. No of conductors  
according to table.  
UL2651

Det.-nr	Ant.	Benämning	Leverantör	Best.-nr
Konstr.	Ritad AS	Godk.	Detaljförteckning	Dat 2020-03-03
				Rev.dat.
				Rev. A
W5    teleanalys			Picoflex cable assemblies	
			Ritn.-nr	CLL-3309-XXX