


SPECIFICATION :
 .CURRENT RATING : 1 AMP.
 .INSULATION RESISTANCE : >1000 MΩ MIN. (AT 500 V DC)
 .DIELECTRIC WITHSTANDING VOLTAGE : AC 500 V MIN. (FOR 1 MINUTE)
 .OPERATING TEMPERATURE : -55°C TO 105°C
 .CONTACT RESISTANCE : ≤ 15mΩ
 .DIELECTRIC MATERIAL : PBT WITH GLASS-FIBER REINFORCED UL 94V-0
 .COLOR : BLACK , BLUE , GRAY (OPTIONAL)
 .CONTACT MATERIAL : PHOSPHOR BRONZE
 .CONTACT PLATING : GOLD OVER NICKEL
 .WIRE SIZE : AWG 26 & 28 STRANDED , 1.27mm CONDUCTOR CENTRE FLAT CABLE

37	63.50/(2.500)	69.40/(2.732)	49.86/(1.963)	47.09/(1.854)	54.60/(2.150)	57.10/(2.248)
25	47.04/(1.852)	53.09/(2.090)	33.24/(1.309)	30.47/(1.200)	38.14/(1.502)	40.90/(1.610)
15	33.32/(1.312)	39.10/(1.539)	19.39/(.763)	16.62/(.654)	24.00/(.945)	26.60/(1.047)
9	24.99/(.984)	30.80/(1.212)	11.08/(.436)	8.31/(.327)	16.10/(.634)	18.60/(.732)
NO. OF POSITIONS	±0.13 A (±.005)	±0.25 B (±.010)	±0.13 C (±.005)	±0.13 D (±.005)	±0.25 E (±.010)	±0.25 F (±.010)



54.84/(2.159)	59.08/(2.328)	60.73/(2.391)
38.38/(1.511)	42.52/(1.674)	44.27/(1.743)
24.66/(.971)	28.80/(1.134)	30.53/(1.202)
18.33/(.743)	20.47/(.806)	22.20/(.874)
H ±0.25 (±.010)	±0.13/(.005) REAR MOUNTING	±0.13/(.005) FRONT MOUNTING

ORDER INFORMATION

C0580 — CONTACT NO: CONTACT TYPE: BODY OPTION: MOUNTING OPTION: CONTACT PLATING: INSULATOR COLOR:

09 , 15 , 25 , 37 F : Female A : Metal Shell W/D S/R B : Metal Shell W/Metal S/R C : Metal Shell W/Plastic S/R D : Plastic Shell W/D S/R E : Plastic Shell W/Metal S/R F : Plastic Shell W/Plastic S/R

A : Through Hole B : Thread Insert 4-40 UNC C : Thread Insert M3 S : Selective Gold G : Gold Flash A : Gold 50µ B : Gold 100µ C : Gold 150µ D : Gold 300µ

B : Black G : Grey L : Blue

FILL IT WITH '0' RoHS Compliant RoHS Compliant

玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.		UNIT		SCALE		PART NAME	
		MM				D-SUB IDC TYPE FEMALE	
制表日: 2006/02/13	DRAWING.	APPROVED	APPD.	CKD.	TOLERANCE	PART NO.	REV.
	<i>John</i>					C0580-XXFXXX0R	A