




## Terminals Series

### KLS8-01106 Female pre-insulating Terminals Series

Maximum Electrical Rating: 75°C 300 Volts Max.  
Insulation Material: Vinyl  
Terminal Material: Brass

VIII



Item No.	Conductor cross-section	Nema tab mm	Thickness of material: T mm	Dimension					Color
				B mm	d mm	D mm	L mm	H mm	
FDD1.25-110 (5)	0.5~1.5mm <sup>2</sup> (22~16A. W. G.) I Max=10A	0.5*2.8	0.3	3.8	1.7	3.8	19	10	Red 
FDD1.25-110 (8)		0.8*2.8	0.3	3.8	1.7	3.8	19		
FDD1.25-187 (5)		0.5*4.75	0.35	5.6	1.7	3.8	19		
FDD1.25-187 (8)		0.8*4.75	0.35	5.6	1.7	3.8	19		
FDD1.25-205		0.5*5.2	0.35	6.5	1.7	3.8	20		
FDD1.25-250		0.8*6.35	0.4	7.4	1.7	3.8	21		
FDD2-110 (5)	1.5~2.5mm <sup>2</sup> (16~14A. W. G.) I Max=15A	0.5*2.8	0.3	3.8	2.3	4.3	19.0	10	Blue 
FDD2-110 (8)		0.8*2.8	0.3	3.8	2.3	4.3	19.0		
FDD2-187 (5)		0.5*4.75	0.35	5.6	2.3	4.3	19.0		
FDD2-187 (8)		0.8*4.75	0.35	5.6	2.3	4.3	19.0		
FDD2-205		0.8*5.2	0.35	6.4	2.3	4.3	20.0		
FDD2-250		0.8*6.35	0.4	7.4	2.3	4.3	21		
FDD2-312		0.8*0.8	0.4	9	2.3	4.3	23.0		
FDD5.5-250	4~6mm <sup>2</sup> (12~10A. W. G.) I Max=24A	0.5*6.35	0.4	7.4	3.4	5.7	25.0	14	Yellow 
FDD5.5-375		1.2*9.4	0.5	10.9	3.4	5.7	29.6		

## ORDER INFORMATION

KLS8-01106 - FDD1.25 - 110 (5)

Item NO.  
Female pre-insulating Terminals Series  
Part Number