
# Speed Controller with One-touch Fittings Series AS Elbow Type/Universal Type Application of the controller with One-touch Fittings

■Applicable tubing O.D.: Metric Size ■Connection thread: M, R

## **How to Order**



#### Elbow type



#### Universal type



## Model

indicates that electroless nickel plated model (N specification) is the standardised.

							<u>'</u>			· · · · · · · · · · · · · · · · · · ·	
Dowt size	Applicable tubing O.D.  Metric size						Applicable cylinder tubing	Elbow type		Universal type	
Port size	3.2		etri 6		ze 10	12	O.D. mm	Meter-out	Meter-in	Meter-out	meter-in
M3 X 0.5	•	•					2.5, 4, 6	AS1201F-M3	AS1211F-M3	AS1301F-M3	AS1311F-M3
M5 X 0.8	•	•	•			l	6, 10, 16, 20	AS1201F-M5	AS1211F-M5	AS1301F-M5	AS1311F-M5
R1/8	•	•	•	•	<b>•</b> *		20, 25, 32	AS2201F-01	AS2211F-01	AS2301F-01	AS2311F-01
R1/4		•	•	•	•		20, 25, 32, 40	AS2201F-02	AS2211F-02	AS2301F-02	AS2311F-02
R1/4			•	•	•	•	40, 50, 63	AS3201F-02	AS3211F-02	AS3301F-02	AS3311F-02
R3/8			•	•	•	•	40, 50, 63	AS3201F-03	AS3211F-03	AS3301F-03	AS3311F-03
R1/2					•	•	63, 80, 100	AS4201F-04	AS4211F-04	AS4301F-04	AS4311F-04

Note 1) \*Elbow type only

Note 2) The meter-out and meter-in types are visually distinguished by the lock nut.

The lock nut of the meter-out type is electroless nickel plated while that of the meter-in type is black zinc chromate plated.

## **Specifications**

<u> </u>	
Proof pressure	1.5 MPa
Max. operating pressure	1 MPa
Min. operating pressure	0.1 MPa
Ambient and fluid temperature	-5 to 60°C (No freezing)
Number of needle rotations	10 rotations (8 rotations Note 1))
Applicable tubing material Note 2)	Nylon, Soft Nylon, Polyurethane
Option	With seal Note 3), Hexagon lock nut, Electroless nickel plated specifications Note 4)

Note 1) In case of types AS1201F-M5 and AS1211F-M5. In case of types AS1301F-M5 and AS1311F-M5.

Note 2) Pay attention to the maximum operating pressure when soft nylon or polyurethane is used (Refer to Best Pneumatics 2004 Vol. 15 for more information.)

Note 3) Types with M3 and M5 port sizes are not available with sealant.

Note 4) Brass parts are all electroless nickel plated

Refer to Best Pneumatics 2004 Vol. 15 for inch sizes.



# **Elbow Type / Universal Type**

AS

JIS symbol	
------------	--



Applicable		Model						
tubing O.D.	Connection thread	Elbow type		Universal type				
mm	uncad	Meter-out	Meter-in	Meter-out	Meter-in			
3.2	M3 X 0.5	AS1201F-M3-23	AS1211F-M3-23	AS1301F-M3-23	AS1311F-M3-23			
	M5 X 0.8	-M5-23	-M5-23	-M5-23	-M5-23			
	R1/8	AS2201F-01-23	AS2211F-01-23	AS2301F-01-23	AS2311F-01-23			
4	M3 X 0.5	AS1201F-M3-04	AS1211F-M3-04	AS1301F-M3-04	AS1311F-M3-04			
	M5 X 0.8	-M5-04	-M5-04	-M5-04	-M5-04			
	R1/8	AS2201F-01-04S	AS2211F-01-04S	AS2301F-01-04S	AS2311F-01-04S			
	R1/4	-02-04S	-02-04S	-02-04S	-02-04S			
6	M5 X 0.8	AS1201F-M5-06	AS1211F-M5-06	AS1301F-M5-06	AS1311F-M5-06			
	R1/8	AS2201F-01-06S	AS2211F-01-06S	AS2301F-01-06S	AS2311F-01-06S			
	R1/4	-02-06S	-02-06S	-02-06S	-02-06S			
	111/4	AS3201F-02-06S	AS3211F-02-06S	AS3301F-02-06S	AS3311F-02-06S			
	R3/8	-03-06S	-03-06S	-03-06S	-03-06S			
8	R1/8	AS2201F-01-08S	AS2211F-01-08S	AS2301F-01-08S	AS2311F-01-08S			
	R1/4	-02-08S	-02-08S	-02-08S	-02-08S			
	111/4	AS3201F-02-08S	AS3211F-02-08S	AS3301F-02-08S	AS3311F-02-08S			
	R3/8	-03-08S	-03-08S	-03-08S	-03-08S			
10	R1/8	AS2201F-01-10S	AS2211F-01-10S					
	R1/4	-02-10S	-02-10S	AS2301F-02-10S	AS2311F-02-10S			
	N 1/4	AS3201F-02-10S	AS3211F-02-10S	AS3301F-02-10S	AS3311F-02-10S			
	R3/8	-03-10S	-03-10S	-03-10S	-03-10S			
	R1/2	AS4201F-04-10S	AS4211F-04-10S	AS4301F-04-10S	AS4311F-04-10S			
12	R1/4	AS3201F-02-12S	AS3211F-02-12S	AS3301F-02-12S	AS3311F-02-12S			
	R3/8	-03-12S	-03-12S	-03-12S	-03-12S			
	R1/2	AS4201F-04-12S	AS4211F-04-12S	AS4301F-04-12S	AS4311F-04-12S			



# **Made to Order**

X12 **Lubricant: Vaseline** 

(Example) AS2201F-01-04S-X12

X214 **Throttle Valve (Without Check Valve)** 

(Example) AS2201F-01-04S-X214

Note) Only items with meter-out part numbers are available in case of throttle valves.

Oil Free (Sealant: PTFE Coated) + Without Check Valve (Throttle Valve)

X21

(Example) AS2201F-01-04S-X21

Note 1) Not a non particle generation type.

Note 2) Only items with meter-out part numbers are available in case of throttle valves.

**Clean Series** 

10-

**Lubricant: Fluororesin grease Double packaging** 

(Example) 10-AS2201F-01-04



AS•FM

AS•F

ASD•F

ASD•FM

ASG AS•FG

ASD•FG

AS•FP

AS•F

AS•FE

ASV•F ASP•F

AS•FT

ASD•FT

AS•FD

ASD•FD

Equipment