

GSM/GPRS Rubber Antenna Specification



Main Technical Specifications

Frequency Range 824-894/1710-1990MHz & 890-960/1710-1890Mhz

Gain 2DB

VSWR $\leq 2.0:1$

Input Impedance 50ohm

Polarization Type Vertical

Bandwidth 70/180Mhz

Max Input power 50w


Antenna Length 50mm


Connector Type SMA R/A male

Antenna weight <10g


Storage Temperature -30°C to +75°C

Characteristic curve






Horizontal Pattern Quad band



Vertical Pattern



单位: m m