

GSM/GPRS Magnetic Antenna Specification



Main Technical Specifications

Frequency Range 824-894/1710-1990MHz & 890-960/1710-1890Mhz

Gain 3DB

VSWR $\leq 1.5:1$

Input Impedance 50ohm

Polarization Type Vertical

Bandwidth 90/280Mhz

Max Input power 60w

Antenna Size $\phi 30 \times 90$ mm

Cable length 2m RG174


Connector Type SMA male

Antenna mounting Magnetic

Antenna color Black

Storage Temperature -30°C to $+75^{\circ}\text{C}$

Characteristic curve



Size drawing

