



M8 MALE FLANGE PLUG FRONT MOUNT

PP wires 4x0.25 0.5m

[Link to Product](#)

Illustration



Product may differ from Image

Form

08562

Technical Data

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

Cables

No./diameter of wires	4 × 0.25 mm ²
Wire isolation	PP (br, wh, bl, bk)
Outer diameter	approx. 1.25 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1