



ENGLISH

Datasheet

Stock No: 243-5537

# RS Pro Line Mounting Hydraulic Flow Control Valve, G 3/8, 350 bar



## Product Details

### High Pressure Flow Control

High pressure flow control valves for general purpose use in a hydraulic system.

Single and double acting versions available

Both ranges have an easy to read colour flow graduation scale and a locking screw to stabilise flow

Nitrile rubber seals

Temp. range -10 to +100°C

0.5 bar cracking pressure

### Flow Control Valves

Single acting and double acting in-line flow control valves. Single acting valves allow flow control in one direction and free flow in the opposite direction. Double acting valves allow flow control in both directions.



ENGLISH

## Specifications:

Manufacturer Series	NDV
Connection Port Thread	G 3/8
Maximum Flow Rate	75L/min
Body Material	Steel
Seal Material	Nitrile Rubber
Maximum Operating Pressure	350 bar
Thread Size	3/8 in
Thread Standard	G
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-10°C