

- Part number : BSI 061806
- Profile / style : British 6 mm
- Connection : Hose barb for hose ID 6 mm
- Description : Compressed air coupling
- Maxi working pressure : 12 bar
- Maxi temperature : +70°C
- Flow @ 6 b with DP 0.6 bar : 750 l/min.
- Safety anti hosewip : ISO 4414
- Locking system : One push button
- Material : Composite body
- Color code : Orange button
- Antistatic
- Meet ATEX 2 standard
- Silicon free
- Non scratch body
- Anti bursting inside cartridge
- Crush and shock resistant
- Positionable body
- No pressure drop designed valve
- GUARANTEE : 3 years zero leak

