






REV:	DESCRIPTION	BY	DATE
V1.0	New issue	SD-02	2022-03-25



Pin	Symbol
1	VCC
2	GND
3	NC
4	SDI
5	SCK
6	CS
7	DC
8	RES

- Notes:
1. Driver IC: SSD1331Z
 2. Type: 0.95"RGB
 3. Interface: 4-wire SPI
 4. The film terminal use "Au Plating"
 5. General Tolerance: ±0.20
 6. The total thickness (1.35 Max) is without Polarizer & Remove Tape.
The actual assembled total thickness with above materials should be 1.70 Max.

		KEEN SIDE electronics	
SHEET: 1 of 1		MODEL NUMBER : KSEOM09502-A8	
APPROVALS		DATE	
DWN	SD-02	2022-03-25	2022-03-25
CHK	SD-11	2022-03-25	2022-03-25
APP	SD-11	2022-03-25	2022-03-25
VERSION: 1.0		UNITS: MM	
GENERAL TOL: ± 0.2		DO NOT SCALE THIS DRAWING.	
SCALE: 1:1		SCALE: 1:1	