


## Cable Ties Series

### KLS8-0901 Cable Ties Series


Material : UL Approved Nylon6/6, 94V-2  
 All nylon, one-piece construction-up to 250 lbs ( 114kgs ) min.  
 loop tensile strength  
 Operating temperature : -40°C to 85°C ( -40 F to 185 F)  
 Specification : UL approved, UV, Heat Resistant, Color are  
 available



1000 pcs/bag	100 pcs/bag	Length mm (inch)	width mm (inch)	Max Bundle Dia mm (inch)	Min. Loop Tensile Strength kg (lbs)
KLS8-0901-80M	KLS8-0901-80MC	80 (3.15)	2.4 (.09)	15 (.59)	8.0 (17-5/8)
KLS8-0901-90M	KLS8-0901-90MC	90 (3.54)	2.4 (.09)	16 (.63)	8.0 (17-5/8)
KLS8-0901-100M	KLS8-0901-100MC	100 (4)	2.5 (.10)	22 (.87)	8.1 (18)
KLS8-0901-120M	KLS8-0901-120MC	120 (4.72)	2.5 (.10)	30 (1.18)	8.1 (18)
KLS8-0901-140M	KLS8-0901-140MC	140 (5.51)	2.5 (.10)	33 (1.30)	8.1 (18)
KLS8-0901-150M	KLS8-0901-150MC	150 (5.9)	2.5 (.10)	35 (1.38)	8.1 (18)
KLS8-0901-160M	KLS8-0901-160MC	160 (6.3)	2.5 (.10)	40 (1.57)	8.1 (18)
KLS8-0901-200M	KLS8-0901-200MC	200 (7.87)	2.5 (.10)	53 (2.09)	8.1 (18)
KLS8-0901-250M	KLS8-0901-250MC	250 (9.84)	2.8 (.11)	65 (2.56)	14 (31)
KLS8-0901-300M	KLS8-0901-300MC	300 (11.81)	2.8 (.11)	76 (2.99)	14 (31)
KLS8-0901-120I	KLS8-0901-120IC	121 (4.76)	3.6 (.14)	30 (1.18)	18.2 (40)
KLS8-0901-140I	KLS8-0901-140IC	140 (5.51)	3.6 (.14)	33 (1.30)	18.2 (40)
KLS8-0901-150I	KLS8-0901-150IC	150 (5.91)	3.6 (.14)	35 (1.38)	18.2 (40)
KLS8-0901-180I	KLS8-0901-180IC	180 (7.09)	3.6 (.14)	44 (1.73)	18.2 (40)
KLS8-0901-200I	KLS8-0901-200IC	200 (7.87)	3.6 (.14)	53 (2.09)	18.2 (40)
KLS8-0901-250I	KLS8-0901-250IC	250 (9.84)	3.6 (.14)	65 (2.56)	18.2 (40)

## ORDER INFORMATION

**KLS8 - 0901 - 80M**



## Cable Ties Series

### KLS8-0901 Cable Ties Series

1000 pcs/bag	100 pcs/bag	Length mm (inch)	width mm (inch)	Max Bundle Dia mm (inch)	Min. Loop Tensile Strength kg (lbs)
KLS8-0901-300I	KLS8-0901-300IC	300 (11.81)	3.6 (.14)	76 (2.99)	18.2 (40)
KLS8-0901-370I	KLS8-0901-370IC	370 (14.57)	3.6 (.14)	102 (4.02)	18.2 (40)
KLS8-0901-120ST	KLS8-0901-120STC	120 (4.72)	4.8 (.19)	24 (.94)	22.2 (50)
KLS8-0901-150ST	KLS8-0901-150STC	150 (5.91)	4.8 (.19)	35 (1.38)	22.2 (50)
KLS8-0901-160ST	KLS8-0901-160STC	160 (6.30)	4.8 (.19)	38 (1.50)	22.2 (50)
KLS8-0901-190ST	KLS8-0901-190STC	188 (7.40)	4.8 (.19)	46 (1.81)	22.2 (50)
KLS8-0901-200ST	KLS8-0901-200STC	200 (7.87)	4.8 (.19)	50 (1.97)	22.2 (50)
KLS8-0901-216ST	KLS8-0901-216STC	215 (8.46)	4.8 (.19)	53 (2.09)	22.2 (50)
KLS8-0901-250ST	KLS8-0901-250STC	250 (9.84)	4.8 (.19)	60 (2.36)	22.2 (50)
KLS8-0901-266ST	KLS8-0901-266STC	265 (10.43)	4.8 (.19)	65 (2.56)	22.2 (50)
KLS8-0901-280ST	KLS8-0901-280STC	280 (11.02)	4.8 (.19)	70 (2.76)	22.2 (50)
KLS8-0901-300ST	KLS8-0901-300STC	300 (11.81)	4.8 (.19)	76 (2.99)	22.2 (50)
KLS8-0901-370ST	-	370 (14.57)	4.8 (.19)	102 (4.02)	22.2 (50)
KLS8-0901-390ST	-	390 (15.35)	4.8 (.19)	105 (4.13)	22.2 (50)
KLS8-0901-430ST	-	430 (16.93)	4.8 (.19)	110 (4.33)	22.2 (50)
KLS8-0901-450ST	-	450 (17.72)	4.8 (.19)	116 (4.57)	22.2 (50)
KLS8-0901-530ST	-	530 (20.87)	4.8 (.19)	140 (5.51)	22.2 (50)
KLS8-0901-550ST	-	550 (21.65)	4.8 (.19)	145 (5.71)	22.2 (50)
KLS8-0901-635ST	-	635 (25)	4.8 (.19)	190 (7.48)	22.2 (50)
KLS8-0901-685ST	-	685 (26.97)	4.8 (.19)	205 (8.07)	22.2 (50)
KLS8-0901-730ST	-	735 (28.94)	4.8 (.19)	224 (8.82)	22.2 (50)
KLS8-0901-830ST	-	830 (32.68)	4.8 (.19)	254 (10)	22.2 (50)
KLS8-0901-150HD	-	150 (5.91)	7.6 (.30)	33 (1.30)	54.4 (120)
KLS8-0901-200HD	-	200 (7.87)	7.6 (.30)	50 (1.97)	54.4 (120)
KLS8-0901-240HD	-	240 (9.45)	7.6 (.30)	63 (2.48)	54.4 (120)
KLS8-0901-250HD	-	250 (9.84)	7.6 (.30)	65 (2.56)	54.4 (120)
KLS8-0901-300HD	-	292 (11.50)	7.6 (.30)	76 (2.99)	54.4 (120)
KLS8-0901-370HD	-	368 (14.49)	7.6 (.30)	102 (4.02)	54.4 (120)
KLS8-0901-430HD	-	430 (16.93)	9.0 (.35)	125 (4.92)	79.4 (175)
KLS8-0901-530HD	-	528 (20.78)	9.0 (.35)	140 (5.51)	79.4 (175)

All specification & dimensions are subject to change, please call your nearest KLS sales representative for update information

## Cable Ties Series

### KLS8-0901 Cable Ties Series

1000 pcs/bag	100 pcs/bag	Length mm (inch)	width mm (inch)	Max Bundle Dia mm (inch)	Min. Loop Tensile Strength kg (lbs)
KLS8-0901-630HD	-	609 (23.97)	9.0 (.35)	178 (7.00)	79.4 (175)
KLS8-0901-710HD	-	710 (27.95)	9.0 (.35)	190 (7.48)	79.4 (175)
KLS8-0901-780HD	-	775 (30.51)	9.0 (.35)	228 (8.98)	79.4 (175)
KLS8-0901-830HD	-	812 (31.97)	9.0 (.35)	239 (9.41)	79.4 (175)
KLS8-0901-920HD	-	912 (35.91)	9.0 (.35)	263 (10.35)	79.4 (175)
KLS8-0901-1020HD	-	1020 (40.16)	9.0 (.35)	295 (11.61)	79.4 (175)
KLS8-0901-1070HD	-	1070 (42)	9.0 (.35)	320 (12.60)	79.4 (175)
KLS8-0901-1220HD	-	1220 (48)	9.0 (.35)	365 (14.37)	79.4 (175)
KLS8-0901-1530HD	-	1530 (60.23)	9.0 (.35)	460 (18.15)	79.4 (175)
KLS8-0901-230EHD	-	230 (9.06)	12.6 (.50)	50 (1.97)	114 (250)
KLS8-0901-290EHD	-	290 (11.42)	12.6 (.50)	76 (2.99)	114 (250)
KLS8-0901-380EHD	-	380 (14.96)	12.6 (.50)	106 (4.17)	114 (250)
KLS8-0901-480EHD	-	480 (18.90)	12.6 (.50)	120 (4.72)	114 (250)
KLS8-0901-580EHD	-	580 (22.83)	12.6 (.50)	152 (5.98)	114 (250)
KLS8-0901-730EHD	-	730 (28.74)	12.6 (.50)	204 (8.03)	114 (250)
KLS8-0901-880EHD	-	880 (34.64)	12.6 (.50)	248 (9.76)	114 (250)
KLS8-0901-1030EHD	-	1030 (40.55)	12.6 (.50)	295 (11.61)	114 (250)
KLS8-0901-290EHD	-	290 (11.42)	12.6 (.50)	76 (2.99)	114 (250)
KLS8-0901-380EHD	-	380 (14.96)	12.6 (.50)	106 (4.17)	114 (250)
KLS8-0901-480EHD	-	480 (18.90)	12.6 (.50)	120 (4.72)	114 (250)
KLS8-0901-580EHD	-	580 (22.83)	12.6 (.50)	152 (5.98)	114 (250)
KLS8-0901-730EHD	-	730 (28.74)	12.6 (.50)	204 (8.03)	114 (250)
KLS8-0901-880EHD	-	880 (34.64)	12.6 (.50)	248 (9.76)	114 (250)
KLS8-0901-1030EHD	-	1030 (40.55)	12.6 (.50)	295 (11.61)	114 (250)