

PSA020AK131AQ



PSA020AK131K



PSR2




PSA063AK441E



PSA050KD334S

Rotary Cam Switches



PSA020AK131S

0-1 On-Off Cam Switches - 60°

Code	Poles	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010AK131S	1 Pole	10	PSK11	✓	
PSA016AK131S	1 Pole	16	PSK11	✓	
PSA020AK131S	1 Pole	20	PSK11	✓	
PSA025AK131S	1 Pole	25	PSK11	✓	
PSA032AK131S	1 Pole	32	PSK21		
PSA040AK131S	1 Pole	40	PSK21		
PSA050AK131S	1 Pole	50	-		
PSA063AK131S	1 Pole	63	-		
PSA080AK131S	1 Pole	80	-		
PSA115AK131S	1 Pole	115	-		



PSA020AK231S

PSA010AK231S	2 Poles	10	PSK11	✓	
PSA016AK231S	2 Poles	16	PSK11	✓	
PSA020AK231S	2 Poles	20	PSK11	✓	
PSA025AK231S	2 Poles	25	PSK11	✓	
PSA032AK231S	2 Poles	32	PSK21		
PSA040AK231S	2 Poles	40	PSK21		
PSA050AK231S	2 Poles	50	-		
PSA063AK231S	2 Poles	63	-		
PSA080AK231S	2 Poles	80	-		
PSA115AK231S	2 Poles	115	-		



PSA020AK331S

PSA010AK331S	3 Poles	10	PSK11	✓	
PSA016AK331S	3 Poles	16	PSK11	✓	
PSA020AK331S	3 Poles	20	PSK11	✓	
PSA025AK331S	3 Poles	25	PSK11	✓	
PSA032AK331S	3 Poles	32	PSK21		
PSA040AK331S	3 Poles	40	PSK21		
PSA050AK331S	3 Poles	50	-		
PSA063AK331S	3 Poles	63	-		
PSA080AK331S	3 Poles	80	-		
PSA115AK331S	3 Poles	115	-		



PSA020AK431S

PSA010AK431S	4 Poles	10	PSK11	✓	
PSA016AK431S	4 Poles	16	PSK11	✓	
PSA020AK431S	4 Poles	20	PSK11	✓	
PSA025AK431S	4 Poles	25	PSK11	✓	
PSA032AK431S	4 Poles	32	PSK21		
PSA040AK431S	4 Poles	40	PSK21		
PSA050AK431S	4 Poles	50	-		
PSA063AK431S	4 Poles	63	-		
PSA080AK431S	4 Poles	80	-		
PSA115AK431S	4 Poles	115	-		



PSA020AK831S


PSA010AK831S	3 Poles + Neutral	10	PSK11	✓	
PSA016AK831S	3 Poles + Neutral	16	PSK11	✓	
PSA020AK831S	3 Poles + Neutral	20	PSK11	✓	
PSA025AK831S	3 Poles + Neutral	25	PSK11	✓	
PSA032AK831S	3 Poles + Neutral	32	PSK21		
PSA040AK831S	3 Poles + Neutral	40	PSK21		
PSA050AK831S	3 Poles + Neutral	50	-		
PSA063AK831S	3 Poles + Neutral	63	-		
PSA080AK831S	3 Poles + Neutral	80	-		
PSA115AK831S	3 Poles + Neutral	115	-		

* Could be supplied with Red-Yellow head w/o extra charge, in this case please replace the "S" at the end with "E"

* 10-25A Cam switches could be supplied with big frame (64x64) with extra charge. In this case please replace the "S" at the end with "B".

* Products are in the Key Operated columns are available for fast mounting Key Head with extra charge. In this case, replace S letter at the end of the code with AQ.

* Please replace S letter at the end of the code with K for Lockable Handle model



PSA020AK141E

0-1 Safety On-Off Cam Switches - 90°

Code	Poles	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010AK141E	1 Pole	10	PSK11		
PSA016AK141E	1 Pole	16	PSK11		
PSA020AK141E	1 Pole	20	PSK11		
PSA025AK141E	1 Pole	25	PSK11		
PSA032AK141E	1 Pole	32	PSK21		
PSA040AK141E	1 Pole	40	PSK21		
PSA050AK141E	1 Pole	50	-		
PSA063AK141E	1 Pole	63	-		
PSA080AK141E	1 Pole	80	-		
PSA115AK141E	1 Pole	115	-		



PSA020AK241E

PSA010AK241E	2 Poles	10	PSK11		
PSA016AK241E	2 Poles	16	PSK11		
PSA020AK241E	2 Poles	20	PSK11		
PSA025AK241E	2 Poles	25	PSK11		
PSA032AK241E	2 Poles	32	PSK21		
PSA040AK241E	2 Poles	40	PSK21		
PSA050AK241E	2 Poles	50	-		
PSA063AK241E	2 Poles	63	-		
PSA080AK241E	2 Poles	80	-		
PSA115AK241E	2 Poles	115	-		



PSA020AK341E

PSA010AK341E	3 Poles	10	PSK11		
PSA016AK341E	3 Poles	16	PSK11		
PSA020AK341E	3 Poles	20	PSK11		
PSA025AK341E	3 Poles	25	PSK11		
PSA032AK341E	3 Poles	32	PSK21		
PSA040AK341E	3 Poles	40	PSK21		
PSA050AK341E	3 Poles	50	-		
PSA063AK341E	3 Poles	63	-		
PSA080AK341E	3 Poles	80	-		
PSA115AK341E	3 Poles	115	-		



PSA020AK441E

PSA010AK441E	4 Poles	10	PSK11		
PSA016AK441E	4 Poles	16	PSK11		
PSA020AK441E	4 Poles	20	PSK11		
PSA025AK441E	4 Poles	25	PSK11		
PSA032AK441E	4 Poles	32	PSK21		
PSA040AK441E	4 Poles	40	PSK21		
PSA050AK441E	4 Poles	50	-		
PSA063AK441E	4 Poles	63	-		
PSA080AK441E	4 Poles	80	-		
PSA115AK441E	4 Poles	115	-		



PSA020AK941E


PSA010AK941E	3 Poles + Neutral	10	PSK11		
PSA016AK941E	3 Poles + Neutral	16	PSK11		
PSA020AK941E	3 Poles + Neutral	20	PSK11		
PSA025AK941E	3 Poles + Neutral	25	PSK11		
PSA032AK941E	3 Poles + Neutral	32	PSK21		
PSA040AK941E	3 Poles + Neutral	40	PSK21		
PSA050AK941E	3 Poles + Neutral	50	-		
PSA063AK941E	3 Poles + Neutral	63	-		
PSA080AK941E	3 Poles + Neutral	80	-		
PSA115AK941E	3 Poles + Neutral	115	-		

* Could be supplied with Red-Yellow head w/o extra charge, in this case please replace the "S" at the end with "E"

* 10-25A Cam switches could be supplied with big frame (64x64) with extra charge. In this case please replace the "S" at the end with "B".

* Products are in the Key Operated columns are available for fast mounting Key Head with extra charge. In this case, replace S letter at the end of the code with AQ.

* Please replace S letter at the end of the code with K for Lockable Handle model



PSA020KD133S

1-2 Changeover Cam Switches - 60°


Code	Poles	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010KD133S	1 Pole	10	PSK11		
PSA016KD133S	1 Pole	16	PSK11		
PSA020KD133S	1 Pole	20	PSK11		
PSA025KD133S	1 Pole	25	PSK11		
PSA032KD133S	1 Pole	32	PSK21		
PSA040KD133S	1 Pole	40	PSK21		
PSA050KD133S	1 Pole	50	-		
PSA063KD133S	1 Pole	63	-		
PSA080KD133S	1 Pole	80	-		
PSA115KD133S	1 Pole	115	-		



PSA020KD333S

PSA010KD233S	2 Poles	10	PSK11		
PSA016KD233S	2 Poles	16	PSK11		
PSA020KD233S	2 Poles	20	PSK11		
PSA025KD233S	2 Poles	25	PSK11		
PSA032KD233S	2 Poles	32	-		
PSA040KD233S	2 Poles	40	-		
PSA050KD233S	2 Poles	50	-		
PSA063KD233S	2 Poles	63	-		

PSA010KD333S	3 Poles	10	PSK12		
PSA016KD333S	3 Poles	16	PSK12		
PSA020KD333S	3 Poles	20	PSK12		
PSA025KD333S	3 Poles	25	PSK12		
PSA032KD333S	3 Poles	32	-		
PSA040KD333S	3 Poles	40	-		
PSA050KD333S	3 Poles	50	-		
PSA063KD333S	3 Poles	63	-		



PSA020KD134S

1-0-2 Changeover Cam Switches - 60°

Code	Poles	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010KD134S	1 Pole	10	PSK11	✓	
PSA016KD134S	1 Pole	16	PSK11	✓	
PSA020KD134S	1 Pole	20	PSK11	✓	
PSA025KD134S	1 Pole	25	PSK11	✓	
PSA032KD134S	1 Pole	32	PSK21		
PSA040KD134S	1 Pole	40	PSK21		
PSA050KD134S	1 Pole	50	-		
PSA063KD134S	1 Pole	63	-		
PSA080KD134S	1 Pole	80	-		
PSA115KD134S	1 Pole	115	-		



PSA020KD234S

PSA010KD234S	2 Poles	10	PSK11	✓	
PSA016KD234S	2 Poles	16	PSK11	✓	
PSA020KD234S	2 Poles	20	PSK11	✓	
PSA025KD234S	2 Poles	25	PSK11	✓	
PSA032KD234S	2 Poles	32	PSK21		
PSA040KD234S	2 Poles	40	PSK21		
PSA050KD234S	2 Poles	50	-		
PSA063KD234S	2 Poles	63	-		
PSA080KD234S	2 Poles	80	-		
PSA115KD234S	2 Poles	115	-		



PSA020KD334S

PSA010KD334S	3 Poles	10	PSK12	✓	
PSA016KD334S	3 Poles	16	PSK12	✓	
PSA020KD334S	3 Poles	20	PSK12	✓	
PSA025KD334S	3 Poles	25	PSK12	✓	
PSA032KD334S	3 Poles	32	PSK22		
PSA040KD334S	3 Poles	40	PSK22		
PSA050KD334S	3 Poles	50	-		
PSA063KD334S	3 Poles	63	-		
PSA080KD334S	3 Poles	80	-		
PSA115KD334S	3 Poles	115	-		

* Could be supplied with Red-Yellow head w/o extra charge, in this case please replace the "S" at the end with "E"

* 10-25A Cam switches could be supplied with big frame (64x64) with extra charge. In this case please replace the "S" at the end with "B".


* Products are in the Key Operated columns are available for fast mounting Key Head with extra charge. In this case, replace S letter at the end of the code with AQ



PSA020KD434S


Code	Poles	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010KD434S	4 Poles	10	PSK12	✓	
PSA016KD434S	4 Poles	16	PSK12	✓	
PSA020KD434S	4 Poles	20	PSK12	✓	
PSA025KD434S	4 Poles	25	PSK12	✓	
PSA032KD434S	4 Poles	32	PSK22		
PSA040KD434S	4 Poles	40	PSK22		
PSA050KD434S	4 Poles	50	-		
PSA063KD434S	4 Poles	63	-		
PSA080KD434S	4 Poles	80	-		
PSA115KD434S	4 Poles	115	-		

Step Cam Switches - 1 Pole




PSA020KS132S

Code	Steps	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010KS132S	0-1-2	10	PSK11	✓	
PSA016KS132S	0-1-2	16	PSK11	✓	
PSA020KS132S	0-1-2	20	PSK11	✓	
PSA025KS132S	0-1-2	25	PSK11	✓	
PSA032KS132S	0-1-2	32	PSK21		
PSA040KS132S	0-1-2	40	PSK21		
PSA050KS132S	0-1-2	50	-		
PSA063KS132S	0-1-2	63	-		
PSA080KS132S	0-1-2	80	-		
PSA115KS132S	0-1-2	115	-		




PSA020KS133S

PSA010KS133S	0-3	10	PSK11	✓
PSA016KS133S	0-3	16	PSK11	✓
PSA020KS133S	0-3	20	PSK11	✓
PSA025KS133S	0-3	25	PSK11	✓
PSA032KS133S	0-3	32	PSK21	
PSA040KS133S	0-3	40	PSK21	
PSA050KS133S	0-3	50	-	
PSA063KS133S	0-3	63	-	
PSA080KS133S	0-3	80	-	
PSA115KS133S	0-3	115	-	




PSA020KS134S

PSA010KS134S	0-4	10	PSK12	✓
PSA016KS134S	0-4	16	PSK12	✓
PSA020KS134S	0-4	20	PSK12	✓
PSA025KS134S	0-4	25	PSK12	✓
PSA032KS134S	0-4	32	PSK22	
PSA040KS134S	0-4	40	PSK22	
PSA050KS134S	0-4	50	-	
PSA063KS134S	0-4	63	-	
PSA080KS134S	0-4	80	-	
PSA115KS134S	0-4	115	-	



PSA020KS135S

PSA010KS135S	0-5	10	PSK12	✓
PSA016KS135S	0-5	16	PSK12	✓
PSA020KS135S	0-5	20	PSK12	✓
PSA025KS135S	0-5	25	PSK12	✓
PSA032KS135S	0-5	32	PSK22	
PSA040KS135S	0-5	40	PSK22	
PSA050KS135S	0-5	50	-	
PSA063KS135S	0-5	63	-	
PSA080KS135S	0-5	80	-	
PSA115KS135S	0-5	115	-	




PSA020KS126S

PSA010KS126S	0-6	10	PSK12	
PSA016KS126S	0-6	16	PSK12	
PSA020KS126S	0-6	20	PSK12	

* Could be supplied with Red-Yellow head w/o extra charge, in this case please replace the "S" at the end with "E".


* 10-25A Cam switches could be supplied with big frame (64x64) with extra charge. In this case please replace the "S" at the end with "B".

* Products are in the Key Operated columns are available for fast mounting Key Head with extra charge. In this case, replace S letter at the end of the code with AQ




PSA020KS127S

Code	Steps	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010KS127S	0-7	10	PSK12		
PSA016KS127S	0-7	16	PSK12		
PSA020KS127S	0-7	20	PSK12		
PSA025KS127S	0-7	25	PSK12		
PSA032KS127S	0-7	32	PSK22		
PSA040KS127S	0-7	40	PSK22		
PSA050KS127S	0-7	50	-		
PSA063KS127S	0-7	63	-		
PSA080KS127S	0-7	80	-		
PSA115KS127S	0-7	115	-		




PSA020KT132S

Step Cam Switches- 60°						
Code	Poles	Rated Thermal Current (A)	Steps	Enclosure	Key Operated	Schema
PSA010KT132S	1 Pole	10	0-1-2	PSK11	✓	
PSA016KT132S	1 Pole	16	0-1-2	PSK11	✓	
PSA020KT132S	1 Pole	20	0-1-2	PSK11	✓	
PSA025KT132S	1 Pole	25	0-1-2	PSK11	✓	
PSA010KT332S	3 Poles	10	0-1-2	PSK12	✓	
PSA016KT332S	3 Poles	16	0-1-2	PSK12	✓	




PSA020MS335S

Star-Delta Cam Switches- 60°					
Code	Steps	Rated Thermal Current (A)	Enclosure	Key Operated	Schema
PSA010MS335S	3 Phase	10	PSK12	✓	
PSA016MS335S	3 Phase	16	PSK12	✓	
PSA020MS335S	3 Phase	20	PSK12	✓	
PSA025MS335S	3 Phase	25	PSK12	✓	
PSA032MS335S	3 Phase	32	PSK22		
PSA040MS335S	3 Phase	40	PSK22		
PSA050MS335S	3 Phase	50	-		
PSA063MS335S	3 Phase	63	-		
PSA080MS335S	3 Phase	80	-		
PSA115MS335S	3 Phase	115	-		



PSA020MS134S

Motor Control Cam Switches- 60°						
Code	Poles	Rated Thermal Current (A)	Steps	Enclosure	Key Operated	Schema
PSA010MS134S	1 Phase	10	1-0-2	PSK11	✓	
PSA016MS134S	1 Phase	16	1-0-2	PSK11	✓	
PSA020MS134S	1 Phase	20	1-0-2	PSK11	✓	
PSA025MS134S	1 Phase	25	1-0-2	PSK11	✓	
PSA032MS134S	1 Phase	32	1-0-2	PSK21		
PSA040MS134S	1 Phase	40	1-0-2	PSK21		
PSA050MS134S	1 Phase	50	-	-		
PSA063MS134S	1 Phase	63	-	-		
PSA080MS134S	1 Phase	80	-	-		
PSA115MS134S	1 Phase	115	-	-		




PSA020MS331S

Code	Poles	Rated Thermal Current (A)	Steps	Enclosure	Key Operated	Schema
PSA010MS331S	3 Phase	10	0-1	PSK11	✓	
PSA016MS331S	3 Phase	16	0-1	PSK11	✓	
PSA020MS331S	3 Phase	20	0-1	PSK11	✓	
PSA025MS331S	3 Phase	25	0-1	PSK11	✓	
PSA032MS331S	3 Phase	32	0-1	PSK21		
PSA040MS331S	3 Phase	40	0-1	PSK21		
PSA050MS331S	3 Phase	50	-	-		
PSA063MS331S	3 Phase	63	-	-		
PSA080MS331S	3 Phase	80	-	-		
PSA115MS331S	3 Phase	115	-	-		

* Could be supplied with Red-Yellow head w/o extra charge, in this case please replace the "S" at the end with "E"


* 10-25A Cam switches could be supplied with big frame (64x64) with extra charge. In this case please replace the "S" at the end with "B".

* Products are in the Key Operated columns are available for fast mounting Key Head with extra charge. In this case, replace S letter at the end of the code with AQ




PSA020MS334S

Code	Poles	Rated Thermal Current (A)	Steps	Enclosure	Key Operated	Schema
PSA010MS334S	3 Phase	10	1-0-2	PSK12	✓	
PSA016MS334S	3 Phase	16	1-0-2	PSK12	✓	
PSA020MS334S	3 Phase	20	1-0-2	PSK12	✓	
PSA025MS334S	3 Phase	25	1-0-2	PSK12	✓	
PSA032MS334S	3 Phase	32	1-0-2	PSK22		
PSA040MS334S	3 Phase	40	1-0-2	PSK22		
PSA050MS334S	3 Phase	50	1-0-2	-		
PSA063MS334S	3 Phase	63	1-0-2	-		
PSA080MS334S	3 Phase	80	1-0-2	-		
PSA115MS334S	3 Phase	115	1-0-2	-		



PSA016CD332S

3 Phase Double Cycle Motor Control Cam Switches (0-1-2)						
Code	Steps	Rated Thermal Current (A)	Enclosure	Key Operated	Schema	
PSA010CD332S	3 Phase	10 A	PSK12	✓		
PSA016CD332S	3 Phase	16 A	PSK12	✓		
PSA020CD332S	3 Phase	20 A	PSK12	✓		
PSA025CD332S	3 Phase	25 A	PSK12	✓		
PSA032CD332S	3 Phase	32 A	PSK22			
PSA040CD332S	3 Phase	40 A	PSK22			
PSA050CD332S	3 Phase	50 A	-			
PSA063CD332S	3 Phase	63 A	-			
PSA080CD332S	3 Phase	80 A	-			
PSA115CD332S	3 Phase	115 A	-			




PSA016CD334S

3 Phase Double Cycle Motor Control Cam Switches (1-0-2)						
Code	Steps	Rated Thermal Current (A)	Enclosure	Key Operated	Schema	
PSA010CD334S	3 Phase	10 A	PSK12	✓		
PSA016CD334S	3 Phase	16 A	PSK12	✓		
PSA020CD334S	3 Phase	20 A	PSK12	✓		
PSA025CD334S	3 Phase	25 A	PSK12	✓		
PSA032CD334S	3 Phase	32 A	PSK22			
PSA040CD334S	3 Phase	40 A	PSK22			
PSA050CD334S	3 Phase	50 A	-			
PSA063CD334S	3 Phase	63 A	-			
PSA080CD334S	3 Phase	80 A	-			
PSA115CD334S	3 Phase	115 A	-			


* Could be supplied with Red-Yellow head w/o extra charge, in this case please replace the "S" at the end with "E"

* 10-25A Cam switches could be supplied with big frame (64x64) with extra charge. In this case please replace the "S" at the end with "B".


* Products are in the Key Operated columns are available for fast mounting Key Head with extra charge. In this case, replace S letter at the end of the code with AQ




PSA0200K421S



PSA0200K422S



PSA0200K426S



PSA0200K723S



PSR1



PSR2



PSK11




PSK21



PSK12



PSK22



PSA020AK131AQ



PSA020AK131K

Measuring Cam Switches - 45°

Code	Type	Rated Thermal Current (A)	Position	Enclosure	Key Operated	Schema
PSA0100K421S	4	10	Voltmeter	PSK11		
PSA0160K421S	4	16	Voltmeter	PSK11		
PSA0200K421S	4	20	Voltmeter	PSK11		
PSA0100K422S	4	10	Phase-Phase Voltmeter	PSK11		
PSA0160K422S	4	16	Phase-Phase Voltmeter	PSK11		
PSA0200K422S	4	20	Phase-Phase Voltmeter	PSK11		
PSA0100K426S	4	10	Amperemeter	PSK12		
PSA0160K426S	4	16	Amperemeter	PSK12		
PSA0200K426S	4	20	Amperemeter	PSK12		
PSA0200K723S	7	20	Voltmeter	PSK12		

Accessories

Code	Type	Features	Material
PSR1	Rail Mounting Interface	Between 10 - 40 A	Plastic
PSR2	Rail Mounting Interface	Between 50 - 63 A	Plastic

Cam Switch Boxes

Code	Material	Features
PSK11	Plastic	IP54
PSK12	Plastic	IP54
PSK21	Plastic	IP54
PSK22	Plastic	IP54
PSK11E	Plastic	IP65
PSK12E	Plastic	IP65
PSK21E	Plastic	IP65
PSK22E	Plastic	IP65