




# ANT-433BNC-Y

## 433MHz ¼ Wave Antenna with BNC

Electrical Specifications	
Frequency Range	433MHz
Nominal Impedance	50 Ω
Maximum Input Power	50W
Polarization	Vertical
Radiation Pattern	Omni
Gain	1.8dBi
VSWR	≤1.5
Connector	BNC

Mechanical Specifications	
Material	TPEE
Antenna dimensions	105mm x 14.4mm
Antenna weight	19g
Ambient Temperature	-40°C to 60°C



<b>Order Code</b>	ANT-433BNC-Y
-------------------	--------------

Accessories	
Description	Order Code

Version	Date	Revision	Known Issues
V1.0	August2013	Initial release	