



CAT6A S/FTP Ultraflex Patch Cable

Technical Features

Cat.6A RJ45 shielded plugs with Cat.7 S/FTP raw cable

Flexible and soft cable with small bending radius

10 Gigabit Ethernet, PoE, PoE+, PoE++

Cat.6A ISO11801 Channel Class EA

EN50173 & ANSI/TIA 568C.2

4x2xAWG26/7 bare copper wire


Low smoke (IEC 61034)

Halogen free (IEC 60754-2)

Flame retardant (IEC 60332-1-2)

Operating temperature: -20°C–75°C

Technical Drawing



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Art-No.	Cable Length	Color	EAN Code
C6A011S	0.25 m	White	4052792055634
C6A021S	0.5 m	White	4052792055641
C6A031S	1 m	White	4052792055658
C6A041S	1.5 m	White	4052792055656
C6A051S	2 m	White	4052792055672
C6A061S	3 m	White	4052792055689
C6A071S	5 m	White	4052792055696
C6A081S	7.5 m	White	4052792055702
C6A091S	10 m	White	4052792055719
C6A101S	15 m	White	4052792055726
C6A111S	20 m	White	4052792055733
C6A121S	30 m	White	4052792055740
C6A141S	50 m	White	4052792055757

Art-No.	Cable Length	Color	EAN Code
C6A012S	0.25 m	Grey	4052792055764
C6A022S	0.5 m	Grey	4052792055771
C6A032S	1 m	Grey	4052792055788
C6A042S	1.5 m	Grey	4052792055795
C6A052S	2 m	Grey	4052792055801
C6A062S	3 m	Grey	4052792055818
C6A072S	5 m	Grey	4052792055825
C6A082S	7.5 m	Grey	4052792055832
C6A092S	10 m	Grey	4052792055849
C6A102S	15 m	Grey	4052792055856
C6A112S	20 m	Grey	4052792055863
C6A122S	30 m	Grey	4052792055870
C6A142S	50 m	Grey	4052792055887



Art-No.	Cable Length	Color	EAN Code
C6A013S	0.25 m	Black	4052792055894
C6A023S	0.5 m	Black	4052792055900
C6A033S	1 m	Black	4052792055917
C6A043S	1.5 m	Black	4052792055924
C6A053S	2 m	Black	4052792055931
C6A063S	3 m	Black	4052792055948
C6A073S	5 m	Black	4052792055955
C6A083S	7.5 m	Black	4052792055962
C6A093S	10 m	Black	4052792055979
C6A103S	15 m	Black	4052792055986
C6A113S	20 m	Black	4052792055993
C6A123S	30 m	Black	4052792056006
C6A143S	50 m	Black	4052792056013

Art-No.	Cable Length	Color	EAN Code
C6A014S	0.25 m	Red	4052792056020
C6A024S	0.5 m	Red	4052792056037
C6A034S	1 m	Red	4052792056044
C6A044S	1.5 m	Red	4052792056051
C6A054S	2 m	Red	4052792056068
C6A064S	3 m	Red	4052792056075
C6A074S	5 m	Red	4052792056082
C6A084S	7.5 m	Red	4052792056099
C6A094S	10 m	Red	4052792056105
C6A104S	15 m	Red	4052792056112
C6A114S	20 m	Red	4052792056129



Art-No.	Cable Length	Color	EAN Code
C6A015S	0.25 m	Green	4052792056136
C6A025S	0.5 m	Green	4052792056143
C6A035S	1 m	Green	4052792056150
C6A045S	1.5 m	Green	4052792056167
C6A055S	2 m	Green	4052792056174
C6A065S	3 m	Green	4052792056181
C6A075S	5 m	Green	4052792056198
C6A085S	7.5 m	Green	4052792056204
C6A095S	10 m	Green	4052792056211
C6A105S	15 m	Green	4052792056228
C6A115S	20 m	Green	4052792056235

Art-No.	Cable Length	Color	EAN Code
C6A016S	0.25 m	Blue	4052792056242
C6A026S	0.5 m	Blue	4052792056259
C6A036S	1 m	Blue	4052792056266
C6A046S	1.5 m	Blue	4052792056273
C6A056S	2 m	Blue	4052792056280
C6A066S	3 m	Blue	4052792056297
C6A076S	5 m	Blue	4052792056303
C6A086S	7.5 m	Blue	4052792056310
C6A096S	10 m	Blue	4052792056327
C6A106S	15 m	Blue	4052792056334
C6A116S	20 m	Blue	4052792056341



Art-No.	Cable Length	Color	EAN Code
C6A017S	0.25 m	Yellow	4052792056358
C6A027S	0.5 m	Yellow	4052792056365
C6A037S	1 m	Yellow	4052792056372
C6A047S	1.5 m	Yellow	4052792056389
C6A057S	2 m	Yellow	4052792056396
C6A067S	3 m	Yellow	4052792056402
C6A077S	5 m	Yellow	4052792056419
C6A087S	7.5 m	Yellow	4052792056426
C6A097S	10 m	Yellow	4052792056433
C6A107S	15 m	Yellow	4052792056440
C6A117S	20 m	Yellow	4052792056457

Art-No.	Cable Length	Color	EAN Code
C6A019S	0.25 m	Purple	4052792056570
C6A029S	0.5 m	Purple	4052792056587
C6A039S	1 m	Purple	4052792056594
C6A049S	1.5 m	Purple	4052792056600
C6A059S	2 m	Purple	4052792056617
C6A069S	3 m	Purple	4052792056624
C6A079S	5 m	Purple	4052792056631
C6A089S	7.5 m	Purple	4052792056648
C6A099S	10 m	Purple	4052792056655
C6A109S	15 m	Purple	4052792056662
C6A119S	20 m	Purple	4052792056679



Package Content

1x CAT6A S/FTP Ultraflex Patch Cable

Packaging Information

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
C6A011S	mm	kg	mm	pcs	kg
C6A021S	mm	kg	mm	pcs	kg
C6A031S	mm	kg	mm	pcs	kg
C6A041S	mm	kg	mm	pcs	kg
C6A051S	mm	kg	mm	pcs	kg
C6A061S	mm	kg	mm	pcs	kg
C6A071S	mm	kg	mm	pcs	kg
C6A081S	mm	kg	mm	pcs	kg
C6A091S	mm	kg	mm	pcs	kg
C6A101S	mm	kg	mm	pcs	kg
C6A111S	mm	kg	mm	pcs	kg
C6A121S	mm	kg	mm	pcs	kg
C6A141S	mm	kg	mm	pcs	kg

