

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 02/01/07	~	LJC 02/01/07
B	整理圖面	YCH 08/15/07	~	


NOTES:

- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 30mΩ Max.INITIAL.
  - DIELECTRIC WITHSTANDING VOLTAGE:500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE:1000MΩ Min.
- MECHANICAL CHARACTERISTICS:
  - DURABILITY: 300 CYCLES.
- ENVIRONMENT CHARACTERISTICS:
  - TEMPERATURE RANGE: -40°C~+105°C.
- PRODUCT NUMBER CODE:  
DS1036 - XX X X X X X X


Position	D±0.2		E±0.2			
	Male	Female	Male	Female		
9P	10.16	30.80	24.99	17.90	16.33	19.00
15P	17.78	39.14	33.32	26.50	24.66	27.34
25P	30.48	53.04	47.04	40.00	38.38	41.24
37P	45.72	69.32	63.50	56.50	54.84	57.52

- SCREW TYPE
- X:W/O SCREW
- 1:CC TYPE
- 2:CS TYPE
- RIVET TYPE
- P:W/ THREAD(UNC #4-40)
- N:W/O THREAD
- CONTACT PLATING
- Si: SELECTIVE GOLD FLASH
- HOUSING COLOR
- U:BLUE
- B:BLACK
- STRAIN RELIEF
- P:W/
- N:W/O
- CONNECTOR TYPE
- M:MALE
- F:FEMALE
- No.OF CONTACTS
- 09:9pos 15:15pos
- 25:25pos 37:37pos

W/O SCREW TYPE




CC TYPE



CS TYPE

UPPER COVER



GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE		I.D.C D-SUB					
X.	±0.60	X.	±3°	mm								
.X	±0.38	.X	±2°	A4	SERIES	DS1036 SERIES						
.XX	±0.25	.XX	±1°									
DRAWING TYPE		CUSTOMER		<b>晨翔电子有限公司</b> <b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b>								
SCALE		1:1							SHEET		1 OF 1	
DRAWING NO.		C-DS1036-XXXXXXX										

Male

Female

