

**Material:**

Housing: PBT+30% Glass filled ,UL94V-0

Contacts: Brass ,

Gold Plating on Contact Area,

Tin on Solder Tail.

Shell: Steel,

Front Shell Nickel Plating,

Back Shell Tin Plating

**Electrical Characteristics:**

Current Rating: 5 AMP


Insulator Resistance: 1000MΩ Min. at DC 500V

Withstanding Voltage: 500V AC (rms) for 1 minute

Contact Resistance: 20mΩ Max. Initial

Operating Temperature: -55°C ~ +105°C

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	—	//		
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.3	0.2	0.3	0.5	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL			NOTE		
DWG.		DATE	SIZE	A4	UNITS	mm	SHEET/OF	1 / 1	
CHK.		DATE	SCALE						
APP.		DATE		 <b>KEEN SIDE</b> electronics					
									NAME
				DWGNO.					