


Material
 Screw: M2.5, Steel, Zn plated
 Shrapnel: Phosphor bronze, Nickel plated
 Pin header: Brass, Tin plated
 Housing: PA66 or PBT, UL94V-0

Electrical
 Rated voltage: 300V
 Rated current: 10A
 Wire range: 28~16AWG 15mm²
 Contact Resistance: 20 mΩ
 Insulation resistance: 500MΩ/DC500V
 Withstand voltage: AC2000V / 1min

Mechanical
 Temp. Range: -40 °C ~ +105 °C
 Torque: 0.4 N.m (3.5Lb. in)
 Strip length: 4.5~5 mm

Order Information



GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		Description:
X: ±0.60	X: ±0.38	X: ±5°	X: ±3°	UNITS	SHEET SIZE	
XX ±0.25		XX ±2°		mm	A4	Screw CONN TERM BLOCK 5.00MM KLS2-332K-5.00-XXP-2S
					KLS P/N:	
Draw by: Date		2015-09-01				
Check by: Date		2015-09-15				
SCALE		SHEET		OF		

KLS ELECTRONIC CO., LTD.