


SECTION A-A

**Material**  
 Pin header: Brass, Tin plated  
 Housing: PA66, UL94V-0  
 Nut: M2.5, Brass

**Electrical**  
 Rated voltage: 300V  
 Rated current: 15A  
 Contact Resistance: 20 mΩ  
 Insulation resistance: 500MΩ/DC500V  
 Withstand voltage: AC2000V / 1 min

**Mechanical**  
 Temp. Range: -40 °C ~ +105 °C  
 Soldering: 250°C 5Sec. Max.

**Order Information**



| GENERAL TOLERANCE        |          | ANGLE TOLERANCE |        | PROJECTION |         | Description:              |
|--------------------------|----------|-----------------|--------|------------|---------|---------------------------|
| X: ±0.60                 | .X ±0.38 | .XX ±0.25       | X: ±5° | .X ±3°     | .XX ±2° |                           |
| Draw by: Date            |          | 2015-09-01      |        | UNITS      | mm      | Plug-in TERM BLOCK 5.08MM |
| Check by: Date           |          | 2015-09-15      |        | SHEET SIZE | A4      |                           |
| SCALE                    |          | SHEET           |        | OF         |         | KLS2-EDGM-5.08-XXP-4      |
| KLS ELECTRONIC CO., LTD. |          |                 |        |            |         |                           |