

Thrust ball bearings, single direction

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Minimum load factor A	Speed ratings		Mass kg	Designation
d	D	H	dynamic	static			Reference speed	Limiting speed		
mm			kN		kN	-	r/min			-
17	30	9	11,4	21,2	0,78	0,0023	8500	12000	0,026	51103

