



ST2-260-LHD-YT

E1518210

STAINLESS STEEL CABLE TIE, 266x7.9mm SS316

Self-locking stainless steel cable ties for use in or outside. The strong locking mechanism includes a steel ball and it is easy to enter the back end that is dawning. This gives a simple, fast and safe installation. Properties cable ties without coating: Material: Stainless steel type 316 Temperature range: -80 degrees Celsius - +500 degrees Celsius (-112° F - +932° F) Colour: Metal



Product Properties:

Model	Without tothing
Material quality	Stainless steel 316 (V4A)
Band closure	Ball latch
UV-stable acc. ASTM D6779	No
Transparent	No
Fluorescent	No
Solvable fastener	No
Text strip	None
Type of fastening	None
Colour	Stainless steel
Surface protection	Untreated
Material	Metal
Halogen free	Yes
Packaging	Loose piece
Inflammability class of insulation material according to with UL94	Other
Operating temperature	-80-538 °C
Mounting temperature	-80-538 °C

Max. tensile force	1110 N
--------------------	--------

Dimensions:

Unit	pcs
Length belt/tape/tie	266 mm
Tie thickness	0.26 mm
Band width	7.9 mm
Max. bundle diameter	69 mm
Max. tensile force	1110 N
MOQ	50 .

Approvals:

With approval according to UL	Yes
MIL approval	No
UL approval	Yes
VG approval	No

Compliance:

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (Latest, 14 June 2023)
SCIP	Not Applicable

Other information:

Trademark	NEMIQ
ETIM-Class	EC000046 - Cable tie
Product Group	Cable ties, steel
Search Description	STÄLBUNTBAND, ROSTFRITT, 266X7.9MM
Alternative SKU	ST2-260-LHD-YT

Logistic information:

Barcode	733117639005
E-no	E1518210
Country of origin	IN
Item status	Stock item, normally in stock with reservation for in between sales.
Packaging	Loose piece
Stock code	ST2-260-LHD-YT
Taric code	73269098
Unit	pcs
MOQ	50 .