



TYPE	L (mm)	A (mm)	
PCHSS-6	6.00	5.00	
PCHSS-10	10.00	4.70	
PCHSS-12	12.00	4.70	
PCHSS-15	15.00	5.00	
PCHSS-20	20.00	5.00	
PCHSS-25	25.00	5.00	
PCHSS-30	30.00	5.00	
PCHSS-50	50.00	5.00	

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	—	//		
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5		

ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTE
DWG.		DATE	SIZE	A4 UNITS mm	SHEET/OF 1 / 1
CHK.		DATE	SCALE	2:1	
APP.		DATE		NAME	PCHSS-XX
			DWGNO.		

