


# FUSE AND FUSE HOLDER

## Φ3.6x10 Glass Tube Fuse Series

KLS5-1005/1006 Inner weld Φ3.6x10 Glass Tube Fuse (Fast Blow) Series




### ELECTRICAL CHARACTERISTICS

RATING	1In	2In	2.75In	4In	10In
BLOWING TIME	Min 4h	Max 5s	Max 300ms	Max 30ms	Max 4ms

Part No.	Rated Current	Iv Voltage Drop	Voltage Rated
1006-0100	100mA	1750	125V/250V
1006-0125	125mA	1500	125V/250V
1006-0150	150mA	1500	125V/250V
1006-0160	160mA	1500	125V/250V
1006-0200	200mA	1500	125V/250V
1006-0250	250mA	1000	125V/250V
1006-0300	300mA	1000	125V/250V
1006-0315	315mA	1000	125V/250V
1006-0350	350mA	1000	125V/250V
1006-0400	400mA	1000	125V/250V
1006-0500	500mA	1000	125V/250V
1006-0600	600mA	900	125V/250V
1006-0700	700mA	500	125V/250V
1006-0750	750mA	500	125V/250V
1006-0800	800mA	275	125V/250V
1006-1000	1A	275	125V/250V
1006-1200	1.2A	275	125V/250V
1006-1250	1.25A	275	125V/250V
1006-1500	1.5A	275	125V/250V
1006-1600	1.6A	275	125V/250V
1006-1800	1.8A	275	125V/250V
1006-2000	2A	250	125V/250V
1006-2500	2.5A	250	125V/250V
1006-3000	3A	250	125V/250V
1006-3150	3.15A	250	125V/250V
1006-3500	3.5A	250	125V/250V
1006-4000	4A	225	125V/250V
1006-5000	5A	225	125V/250V
1006-6000	6A	225	125V/250V
1006-6300	6.3A	200	125V/250V
1006-7000	7A	200	125V/250V
1006-8000	8A	200	125V/250V
1006-10000	10A	200	125V/250V
1006-12000	12A	180	125V/250V
1006-15000	15A	180	125V/250V

Part No.	Rated Current	Iv Voltage Drop	Voltage Rated
1005-0100	100mA	1750	125V/250V
1005-0125	125mA	1500	125V/250V
1005-0150	150mA	1500	125V/250V
1005-0160	160mA	1500	125V/250V
1005-0200	200mA	1500	125V/250V
1005-0250	250mA	1000	125V/250V
1005-0300	300mA	1000	125V/250V
1005-0315	315mA	1000	125V/250V
1005-0350	350mA	1000	125V/250V
1005-0400	400mA	1000	125V/250V
1005-0500	500mA	1000	125V/250V
1005-0600	600mA	900	125V/250V
1005-0700	700mA	500	125V/250V
1005-0750	750mA	500	125V/250V
1005-0800	800mA	275	125V/250V
1005-1000	1A	275	125V/250V
1005-1200	1.2A	275	125V/250V
1005-1250	1.25A	275	125V/250V
1005-1500	1.5A	275	125V/250V
1005-1600	1.6A	275	125V/250V
1005-1800	1.8A	275	125V/250V
1005-2000	2A	250	125V/250V
1005-2500	2.5A	250	125V/250V
1005-3000	3A	250	125V/250V
1005-3150	3.15A	250	125V/250V
1005-3500	3.5A	250	125V/250V
1005-4000	4A	225	125V/250V
1005-5000	5A	225	125V/250V
1005-6000	6A	225	125V/250V
1005-6300	6.3A	200	125V/250V
1005-7000	7A	200	125V/250V
1005-8000	8A	200	125V/250V
1005-10000	10A	200	125V/250V
1005-12000	12A	180	125V/250V
1005-15000	15A	180	125V/250V



## ORDER INFORMATION

Product NO.: KLS5-1005-XXXX

Rated Current  
Lead Type: 1005=With Lead 1006=No Lead  
Part Number