

AK-707-A-SSB-WP-MM




AK-707-N-SSB-WP-MM

GENERAL SPECIFICATION

- Contact rating: 20mA, 24VDC
- Contact resistance: 200 ohm max
- Life: 2,000,000 cycles per key
- Operating Temperature: -20°C to +60°C
- Storage Temperature: -40°C to +65°C


STANDARD MATRIX CIRCUIT DIAGRAM

CIRCUIT DIAGRAM



AK-707

OUTPUT ARRANGEMENT	
OUTPUT PIN NO.	SYMBOL
1	COL 2
2	ROW 1
3	COL 1
4	ROW 4
5	COL 3
6	ROW 3
7	ROW 2



ACTUATING FORCE: 150 ± 30 GRAMS.
STROKE: 2.0 ± 0.5mm