

ACCORD

ACCORD CO., LTD.




AK-304-N-WWB

**GENERAL SPECIFICATION**


- Contact rating: 20mA, 24VDC
- Contact resistance: 200 ohm max
- Life: 1,000,000 cycles per key
- Operating Temperature: -20°C to +60°C
- Storage Temperature: -40°C to +65°C

**STANDARD MATRIX CIRCUIT DIAGRAM**



AK-304

| OUTPUT ARRANGEMENT |         |        |
|--------------------|---------|--------|
| OUTPUT             | PIN NO. | SYMBOL |
| 1                  |         | COL 2  |
| 2                  |         | ROW 1  |
| 3                  |         | COL 1  |
| 4                  |         | ROW 4  |
| 5                  |         | COL 3  |
| 6                  |         | ROW 3  |
| 7                  |         | ROW 2  |



ACTUATING FORCE: 100 ± 30 GRAMS.  
STROKE: 1.4 ± 0.4 mm

СЕТЬ ЭЛЕКТРОННЫХ КОМПОНЕНТОВ **СЭлКом**

ООО "СЭлКом"  
+7 495 204-1384  
radiodetali.com  
sale@radiodetali.com

" RoHS Compliant "