




brass accessories

0121 male straight adapter — NPT to BSPT




C1 NPT	C2 BSPT		F mm	L mm	kg
1/8	R1/4	0121 11 10	11	19	.009
1/4	R1/4	0121 14 13	14	27	.021
3/8	R3/8	0121 18 17	17	28	.025
1/2	R1/2	0121 22 21	22	36	.053
3/4	R3/4	0121 28 27	27	40	.090

0121 male straight adapter — BSPT




C1 BSPT	C2 BSPT		F mm	L mm	kg
R1/8	R1/8	0121 10 10	11	19	.009
R1/4	R1/4	0121 13 13	14	27	.021
R1/4	R1/8	0121 13 10	14	23.5	.021
R3/8	R3/8	0121 17 17	17	28	.025
R3/8	R1/4	0121 17 13	17	27.5	.024
R3/8	R1/8	0121 17 10	17	24	.022
R1/2	R1/2	0121 21 21	22	36	.053
R1/2	R3/8	0121 21 17	22	32.5	.045
R1/2	R1/4	0121 21 13	22	32	.045
R1/2	R1/8	0121 21 10	22	28.5	.041
R3/4	R3/4	0121 27 27	27	40	.092
R3/4	R1/2	0121 27 21	27	39	.084
R3/4	R3/8	0121 27 17	27	35.5	.076
R3/4	R1/4	0121 27 13	27	35	.079
R1"	R1"	0121 34 34	36	46	.156
R1"	R3/4	0121 34 27	36	43	.143
R1"	R1/2	0121 34 21	36	42	.133
R1"	R3/8	0121 34 17	36	38.5	.126
R1"1/4	R1"1/4	0121 42 42	46	53	.233
R1"1/4	R1"	0121 42 34	46	50.5	.237
R1"1/4	R3/4	0121 42 27	46	47.5	.229
R1"1/4	R1/2	0121 42 21	46	46.5	.219

0929 3 piece adapter — double male BSPT




C BSPT		F mm	F1 mm	H mm	H1 mm	H2 mm	kg
R1/8	0929 00 10	15	5	27	9	8.5	0.181
R1/4	0929 00 13	19	6	33.5	11.5	9.5	0.100
R3/8	0929 00 17	22	8	36.5	13	10	0.010
R1/2	0929 00 21	27	12	45	15.5	12	0.088

0155 female sleeve — BSPP



C BSPP		F mm	L mm	kg
G1/8	0155 10 10	14	17	.015
G1/4	0155 13 13	17	24	.025
G3/8	0155 17 17	22	25	.045
G1/2	0155 21 21	27	32	.084
G3/4	0155 27 27	32	35	.109

0164 adapter — female BSPP to male NPT



C1 NPT	C2 BSPP		E mm	F mm	L mm	kg
1/8	G1/8	0164 11 10	7.5	14	20	.015
1/4	G1/4	0164 14 13	11	17	27.5	.028
3/8	G3/8	0164 18 17	11.5	22	28.5	.044
1/2	G1/2	0164 22 21	15	27	36.5	.081
3/4	G3/4	0164 28 27	16.5	32	38.5	.112