



Sample photo

Order symbol: PC 081206
Product nbr: 7032580
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074003621
EI. number:
 Finland: 3423428
 Electric No. Denmark: 8212002623
 Electric No. Italy: 7301020
 Electric No. Sweden: 2536111

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		120	80	55	Ingress Protection (EN 60529): IP66/IP67
inch:		4.7	3.1	2.2	Impact Resistance (EN 62262): IK07/IK08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:		RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:		Stainless steel			Flammability Rating: UL 746C 5V
Cover colour:		RAL 7035 -light grey			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Temperature °C (short term):		-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):		-40 ... 80 °C			Gost R
Temperature °F (short term):		-40 ... 250 °F			
Temperature °F (continuous):		-40 ... 175 °F			

