

Film Capacitors

CCC-21

(1 Flap FL16/20) 16 Values / 405 Pieces

Polyester Film Capacitors for 100V-DC / Dipped Capacitor element with radial leads

Type/Brand: PEI / Prestige

Tolerance: ±10%

Temperature: -40 to +85°C

Values-Quantities Selection:

1,0nF	50x	4,7nF	50x	22nF	25x	0,10uF	25x
1,5nF	20x	6,8nF	20x	33nF	20x	0,15uF	10x
2,2nF	30x	10 nF	50x	47nF	25x	0,22uF	10x
3,3nF	20x	15 nF	20x	68nF	20x	0,47uF	10x

CCC-23

(1 Flap FL24/10) 24 Values / 230 Pieces

Polypropylene Film Capacitors for 100V-DC / Dipped Capacitor element with radial leads

Type/Brand: CBB11 / Prestige

Tolerance: ±5%

Temperature: -40 to +85°C

Values-Quantities Selection:

1,0nF	20x	2,2nF	15x	4,7nF	15x	10nF	16x	22nF	8x	47nF	8x
1,2nF	10x	2,7nF	10x	5,6nF	8x	12nF	6x	27nF	5x	56nF	4x
1,5nF	15x	3,3nF	15x	6,8nF	12x	15nF	8x	33nF	8x	68nF	5x
1,8nF	10x	3,9nF	8x	8,2nF	8x	18nF	6x	39nF	5x	0,1uF	5x

REV: 30.11.2010

CCC-41a

(1 Flap FL16/10) 22 Values / 525 Pieces
Multi-Layer MKT Capacitors

Type/Brand: B32529...X-Y / Epcos

Tolerance: ±10%

Temperature: -55 to +100°C

Pitch: 5mm

Capacitance	Voltage	Capacitance	Voltage
1,0nF-6,8nF	400V	0,1uF-0,47uF	63V
10nF-33nF	250V	1,5uF	63V
47nF-68nF	100V	0,68uF-3,3uF	63V

Values-Quantities Selection:

1,0nF	30x	1,5nF	20x	2,2nF	30x	3,3nF	20x	4,7nF	30x	6,8nF	20x
10nF	30x	15nF	20x	22nF	30x	33nF	20x	47nF	30x	68nF	20x
0,1uF	80x	0,15uF	20x	0,22uF	20x	0,33uF	15x	0,47uF	20x	0,68uF	20x
1,0uF	20x	1,5uF	10x	2,2uF	10x	3,3uF	10x				

CCC-51

(1 Flap FL16/10) 16 Values / 600 Pieces
Metallized polyester capacitor / Plastic case with radial leads

Type/Brand: MKS 02 / WIMA

Tolerance: ±20%

Temperature: -55 to +100°C

Pitch: 2,5mm

Values-Quantities Selection:

1,0nF/250V	50x	2,2nF/250V	25x	3,3nF/250V	25x	4,7nF/250V	50x
10nF/63V	50x	15nF/63V	25x	22nF/63V	50x	33nF/63V	25x
47nF/63V	50x	68nF/63V	25x	100nF/63V	50x	150nF/50V	25x
220nF/50V	50x	330nF/50V	25x	470nF/50V	50x	680nF/50V	25x

REV: 30.11.2010

CCC-52

(1 Flap FL16/10) 16 Values / 440 Pieces
Metallized polyester capacitor / Plastic case with radial leads

Type/Brand: MKS 2 / WIMA

Tolerance: +/-10%

Temperature: -55 to +100°C

Pitch: 5mm

Values-Quantities Selection:

10nF/63V	50x	15nF/63V	25x	22nF/63V	50x	33nF/63V	25x
47nF/63V	50x	68nF/63V	25x	100nF/63V	50x	150nF/63V	25x
220nF/63V	25x	330nF/63V	20x	470nF/63V	25x	680nF/63V	20x
1,0uF/63V	20x	1,5uF/63V	10x	2,2uF/63V	10x	3,3uF/63V	10x

CCC-61

(1 Flap FL16/20) 8 Values / 135 Pieces
Dipped MKP Capacitors for 250V-AC

Type/Brand: Y1 / TEAPO

Tolerance: ±10%

Temperature: -25 to +70°C

Values-Quantities Selection:

0,1uF	30x	0,15uF	25x	0,22uF	20x	0,33uF	20x
0,47uF	15x	0,68uF	10x	1,0uF	10x	2,0uF	5x

CCC-62

(1 Flap FL16/20) 7 Values / 83 Pieces
Dipped MKP Capacitors for 400V-AC

Type/Brand: Y1 / TEAPO

Tolerance: ±10%

Temperature: -25 to +70°C

Values-Quantities Selection:

0,1uF	20x	0,15uF	15x	0,22uF	12x	0,33uF	8x
0,47uF	8x	0,68uF	8x	1uF	12x		

REV: 30.11.2010

YE discontinued, substitute MK

CCC-63

(1 Flap FL16/20) 9 Values / 105 Pieces
MKP Capacitors in rectangular plastic case for 250V-AC

Type/Brand: YE-DS / TEAPO or
MK / SEIKA

Tolerance: $\pm 10\%$

Temperature: -40 to +85°C

Values-Quantities Selection:

0,1uF	15x	0,15uF	15x	0,22uF	15x	0,33uF	8x
0,47uF	18x	0,68uF	6x	1,0uF	18x	1,5uF	4x
2,0uF	6x						

CCC-64

(1 Flap FL16/20) 7 Values / 71 Pieces
MKP Capacitors in rectangular plastic case for 400V-AC

Type/Brand: YE-DS / TEAPO or
MK / SEIKA

Tolerance: $\pm 10\%$

Temperature: -40 to +85°C

Values-Quantities Selection:

0,1uF	15x	0,15uF	15x	0,22uF	15x	0,33uF	8x
0,47uF	6x	0,68uF	4x	1,0uF	8x		

REV: 30.11.2010