

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192160003](#)
Status: **Active**
Overview: [Splices](#)
Description: Multi-Lock Connector for 14-16 AWG Wire

Documents:

[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family [Splices](#)
Series [19216](#)
Comments 13.97 x 9.53mm when closed
Crimp Quality Equipment Yes
Overview [Splices](#)
Product Name Multi-Lock
UPC 800753056138

Physical

Barrel Type Closed
Color - Resin Blue
Flammability 94V-0
Insulation Polypropylene
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1.267/g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 3.30mm & 4.32mm
Wire Size AWG 14, 16
Wire Size mm² N/A

Electrical

Voltage - Maximum 600V

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number ML-1814

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19216-003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19216 Series](#)