





Standard withdrawn



BN 3
Hex socket head cap screws
fully threaded
Steel 8.8
zinc plated blue
<ul style="list-style-type: none"> • ~UNI 5931 • ~ČSN 021143



M18: not included in ISO 4762

Article#	d ₁	d ₂	k	s	t min.	L
1003739	M3	5,5	3	2,5	1,3	4
1003747						5
1003755						6
1003763						8
1003771						10
1003798						12
1003801						(14)
1003828						16
1301683						(18)
1301691						20
2108186						(22)
3054701						25
1003887	M4	7	4	3	2	5
1003895						6
1003909						8
1003917						10
1003925						12
1003933						(14)
1003941						16
1003968						(18)
1003976						20
1301705						(22)
1301713						25
3054702						30
8278563						40
1004050	M5	8,5	5	4	2,5	6

M18: not included in ISO 4762

Article#	d ₁	d ₂	k	s	t min.	L
1004069	M5	8,5	5	4	2,5	8
1004077						10
1004085						12
1004093						(14)
1004107						16
1004115						(18)
1004123						20
1004131						(22)
1004158						25
1004166						30
3054704						35
1004247	M6	10	6	5	3	6
1004255						8
1004263						10
1004271						12
1004298						(14)
1004301						16
1004328						(18)
1004336						20
1004344						(22)
1004352						25
1004360						30
3186744						35
1542257						40
8276234						45
1542265						50
3054705						60
5514688						80
1004514	M8	13	8	6	4	10
1004522						12
1004530						(14)
1004549						16
1004557						(18)
1004565						20
1004573						(22)
1004581						25
1004603						30
1004611						35
1004638						40
3186746						45
1004646						50

M18: not included in ISO 4762

Article#	d ₁	d ₂	k	s	t min.	L
3054706	M8	13	8	6	4	60
3186749						70
1004816	M10	16	10	8	5	12
1004824						(14)
1004832						16
1004840						(18)
1004859						20
1004867						(22)
1004875						25
1004883						30
1004891						35
1004905						40
3378224						45
1004913						50
3054707						60
1005065	M12	18	12	10	6	16
1005073						20
1005103						25
1005111						30
1005138						35
1005146						40
1301721						45
1005154						50
3054708						60
1005324	(M14)	21	14	12	7	25
1005332						30
1005340						35
1005359						40
1005367						45
1301748						50
1301969						55
1005499	M16	24	16	14	8	25
1005502						30
1005510						35
1005529						40
1005537						45
1005545						50
1301756						55
1471260						60
3054709						70
1005693	(M18)	27	18	14	9	40

M18: not included in ISO 4762

Article#	d ₁	d ₂	k	s	t min.	L
1005707	(M18)	27	18	14	9	45
1005715						50
1301764						60
1005812	M20	30	20	17	10	35
1005820						40
1005839						45
1005847						50
1005855						55
1005863						60
5503588						65
1479008						70
1005987	M24	36	24	19	12	40
9019995						45
1005995						50
1006002						60
1006010						70
1301772						80
8211345						100