



XLRM AND XLRF WIRING CHART							
JACKET COLOR	H.S. TUBING MARKING	END "A" XLR MALE			END "B" XLR FEMALE		
		RED	BLACK	BARE	RED	BLACK	BARE
BROWN	CHANNEL 1	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
RED	CHANNEL 2	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
ORANGE	CHANNEL 3	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
YELLOW	CHANNEL 4	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
GREEN	CHANNEL 5	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
BLUE	CHANNEL 6	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
PURPLE	CHANNEL 7	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"
GRAY	CHANNEL 8	PIN "2"	PIN "3"	PIN "1"	PIN "2"	PIN "3"	PIN "1"

NOTES:

- CABLE BREAKOUT LENGTH IS 18.00 +/- 0.75 IN.
- CABLE IS SHIPPED COILED AND PACKAGED IN A BAG.
- MATERIALS:
 - HANDLES - ZINC ALLOY, SEE TABLE FOR FINISH
 - INSULATORS AND HEAT SHRINK TUBING - THERMOPLASTIC
 - XLR MALE CONNECTOR:
 - HOUSING - ZINC ALLOY
 - GROUND TERMINAL - SPECIAL COPPER ALLOY
 - CONTACT PINS - COPPER ALLOY, SEE TABLE FOR FINISH
 - XLR FEMALE CONNECTOR:
 - CABLE CLAMP AND FLEX RELIEF - THERMOPLASTIC, BLACK
 - HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED
 - GROUND TERMINAL - SPECIAL COPPER ALLOY, ELECTRO-TINNED
 - SOCKET CONTACTS - SPECIAL COPPER ALLOY, SEE TABLE FOR FINISH
 - O-RING - THERMOPLASTIC RUBBER, BLACK
 - CABLE - COPPER, THERMOPLASTIC
- THIS PRODUCT IS RoHS COMPLIANT.

PART NUMBER	CABLE LENGTH "X"	XLR MALE FINISH	XLR FEMALE FINISH
XLRM05XLRF	5.00 FT +/- 1.50 IN	NICKEL HANDLE, SILVER PINS	NICKEL HANDLE, SILVER SOCKETS
XLRM10XLRF	10.00 FT +/- 1.50 IN	NICKEL HANDLE, SILVER PINS	NICKEL HANDLE, SILVER SOCKETS
XLRM05XLRFB	5.00 FT +/- 1.50 IN	BLACK HANDLE, GOLD PINS	BLACK HANDLE, GOLD SOCKETS
XLRM10XLRFB	10.00 FT +/- 1.50 IN	BLACK HANDLE, GOLD PINS	BLACK HANDLE, GOLD SOCKETS

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					SIZE	WIDTH	MULT	LBS/M	TEMPER	
					UNLESS OTHERWISE SPECIFIED				MATERIAL SPEC No.	
					1. ALL DIMENSIONS IN INCHES				SCALE 1:2	
					- TWO PLACE DECIMALS ±0.02				Switchcraft®	
					- THREE PLACE DECIMALS ±0.005				SHEET 1 OF 1	
B	26637	10/11/10	RS	TJK	DATE DRAWN	BY	CHKD	APVD	PART No.	
A	25983	10/3/08	RS	TJK	4/14/08	JGK	RS	TJK	XLRM_XLRF SERIES	
REV	ECO NUMBER	DATE	BY	APVD	NAME		XLR MALE TO XLR FEMALE, RoHS		REV	
REVISIONS					DO NOT SCALE DRAWING					B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[XLRM05XLRFB](#) [XLRM05XLRFB](#) [XLRM10XLRFB](#) [XLRM10XLRFB](#)