


Self-aligning ball bearings, cylindrical and tapered bore, cylindrical bore, seal on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
10	30	14	5,53	1,18	0,06	-	17000	0,048	2200 E-2RS1TN9



Calculation factors

- e 0,33
- Y_1 1,9
- Y_2 3
- Y_0 2