



Self-aligning ball bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
30	62	20	15,6	4,65	0,24	-	7500	0,26	2206 E-2RS1TN9



Calculation factors

- e 0,25
- Y₁ 2,5
- Y₂ 3,9
- Y₀ 2,5