



Shell size	$A^{+0.76}_0$	$B^{+0.25}_0$	$C \pm 0.12$	$F \pm 0.12$	$G^{+0.25}_0$	$L^{+0.22}_0$	Part Number
E	30.43	16.21	24.99	10.96	6.05	0.80	86553148TLF
A	38.76	24.54	33.32	10.96	6.05	0.80	86553149TLF
B	52.65	38.25	47.04	10.96	6.05	0.80	86553150TLF
C	68.94	54.71	63.50	10.96	6.05	0.80	86553151TLF

NOTES

- RoHS INFO : The product meets the european directives and others countries regulations as described on the GS-47-0004
- The product isn't intended to be exposed to a manufacturing solder process
- Plating : Sn pure bright over copper
- Packaging spec : see GS-14-920

spec ref	-	dr	A Parrenin	2013/04/04	projection	mm	size	A3	scale	2:1	
tolerance std	ISO 406 ISO 1101	eng	A Parrenin	2013/05/16			ecn no	ELX-B-14776-1			
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr	Laurent Mulin	2013/05/16			product family	D-Sub	rel level	Released	
surface	ISO 1302	appr	Gert Dreesbeke	2013/05/16	SOCKET METAL CAPS		dwg no	C01-8655-1657		rev	D
	linear	0.X	±0.3		D SUB ACCESSORIES		cat. no.	-		Product - Customer Drw	sheet 1 of 1
		0.XX	±0.10								
	angular	0°	±2°								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86553148TLF](#) [86553149TLF](#) [86553150TLF](#) [86553151TLF](#)