

Customer Information Sheet

DRAWING No.: M80-866XXXX

IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:

MATERIAL:
 MOULDING = GLASS-FILLED POLYESTER,
 UL94V-0, BLACK

CONTACTS = PHOSPHOR BRONZE
 LATCHES = BERYLLIUM COPPER

FINISH:

CONTACTS:
 05 = 0.75µm GOLD
 22 = 0.75µm GOLD ON CONTACT AREA.
 3.0µm 90/10 TIN/LEAD ON TAILS
LATCH = 1.25µm NICKEL

ELECTRICAL:

CURRENT RATING (25°C) = 3.0A MAX.
 CURRENT RATING (85°C) = 2.2A MAX.
 WORKING VOLTAGE = 800V AC/DC
 VOLTAGE PROOF = 1200V AC/DC

CONTACT RESISTANCE:

INITIAL = 20 mΩ MAX.
 AFTER CONDITIONING = 25 mΩ MAX.
INSULATION RESISTANCE:
 INITIAL = 1000 MΩ MIN.
 AFTER CONDITIONING = 100 MΩ MIN.

MECHANICAL:


DURABILITY = 500 OPERATIONS

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

TUBE
 FOR COMPLETE SPECIFICATION, SEE COMPONENT
 SPECIFICATION C005XX (LATEST ISSUE)



NOTES:

- 2-OFF STRAIN RELIEF STRAPS M80-0030006 ARE INCLUDED WITH THIS CONNECTOR.
- FOR RoHS COMPLIANT EQUIVALENT PRODUCT USE M80-851XXXX CONNECTORS.

BRITISH STANDARD ORDER CODE:
B5743-2XX-M-L-X

TOTAL No. OF WAYS _____
 04, 06, 08, 10, 12, 14, 16,
 18, 20, 26, 34, 44

FINISH: _____
 1 = SELECTIVE GOLD + TIN/LEAD
 3 = GOLD

ORDER CODE:
M80-866XXXX

TOTAL No. OF WAYS _____
 04, 06, 08, 10, 12, 14, 16,
 18, 20, 26, 34, 44

FINISH: _____
 05 = GOLD
 22 = SELECTIVE GOLD & TIN/LEAD

MGP	14	01.12.21	31135
NAME	ISS.	DATE	CN/CO
APPROVED: MGP			
CHECKED: RA			
DRAWN: K. SHIER			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
 technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
 X. = ±1mm
 X.X = ±0.50mm
 X.XX = ±0.20mm
 X.XXX = ±0.01mm
ANGLES = ±5°
 UNLESS STATED

MATERIAL:
 SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE: DATAMATE DIL
 HORIZONTAL MALE PC TAIL
 ASSEMBLY - LATCHED

DRAWING NUMBER:
M80-866XXXX

SHT
 2
 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M80-8663422](#) [M80-8662022](#) [M80-8660422](#) [M80-8661822](#) [M80-8661422](#) [M80-8661205](#) [M80-8661622](#) [B5743-218-M-L-3](#) [B5743-218-M-L-1](#) [B5743-208-M-L-1](#) [B5743-212-M-L-1](#) [B5743-216-M-L-1](#) [B5743-214-M-L-1](#) [B5743-210-M-L-1](#) [B5743-234-M-L-3](#) [B5743-234-M-L-1](#) [B5743-204-M-L-1](#) [B5743-206-M-L-1](#) [B5743-220-M-L-3](#) [B5743-220-M-L-1](#) [B5743-226-M-L-1](#) [M80-8660605](#) [B5743-206-M-L-3](#) [M80-8661605](#) [M80-8661022](#) [M80-8660622](#) [M80-8662622](#) [M80-8660822](#) [M80-8661222](#) [M80-8664422](#) [M80-8662605](#) [B5743-210-M-L-3](#) [B5743-216-M-L-3](#) [M80-8661405](#) [B5743-204-M-L-3](#) [B5743-212-M-L-3](#) [B5743-226-M-L-3](#) [B5743-214-M-L-3](#) [B5743-208-M-L-3](#) [M80-8661005](#) [M80-8662005](#)