



## S8VK-T12024

Book type power supply, Pro, 120 W, 24VDC, 5A, DIN rail mounting

# Specifications

Type	Book type
Mounting method	DIN rail
Phase	Three
Power output	120 W
Efficiency	89 %
Output voltage	24 V
Rated output current	5 A
Power boost ratio	120 %
Temperature range	-40-70 °C
Terminal	Screw
Rated supply voltage at AC 50 Hz	380-480 V
Allowable supply voltage AC	320-576 V
Allowable supply voltage DC	450-810 V
Product Width (unpacked)	40 mm
Product Height (unpacked)	125 mm
Product Depth (unpacked)	113 mm

# Accessories

**S82Y-VK10F**

Front-mounting bracket for S8VK (120, 240 and 480 W models)

# Related products



## Electronic Circuit Breaker

S8V-CP - Electronic Circuit Breaker

# Downloads

CAD Library



### Perfect Power Supply Solutions Brochure

EN PDF 807 KB



### S8VK-S/S8FS-G Brochure

EN PDF 6.93 MB



### S8VK-T Switch Mode Power Supply Datasheet

EN PDF 4.07 MB

#### TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 15 May, 2023. Click here for [terms of use](#).

**OMRON**

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU