



## S8VK-T48024

Book type power supply, Pro, 480 W, 24VDC, 20A, DIN rail mounting

# Specifications

|                                  |           |
|----------------------------------|-----------|
| Type                             | Book type |
| Mounting method                  | DIN rail  |
| Phase                            | Three     |
| Power output                     | 480 W     |
| Efficiency                       | 91 %      |
| Output voltage                   | 24 V      |
| Rated output current             | 20 A      |
| Power boost ratio                | 120 %     |
| Temperature range                | -40-70 °C |
| Terminal                         | Screw     |
| Rated supply voltage at AC 50 Hz | 380-480 V |
| Allowable supply voltage AC      | 320-576 V |
| Allowable supply voltage DC      | 450-810 V |
| Product Width (unpacked)         | 95 mm     |
| Product Height (unpacked)        | 125 mm    |
| Product Depth (unpacked)         | 140 mm    |

## Accessories

**S82Y-VK10F**

Front-mounting bracket for S8VK (120, 240 and 480 W models)

# Related products



## Electronic Circuit Breaker

S8V-CP - Electronic Circuit Breaker

# Downloads

CAD Library



### Perfect Power Supply Solutions Brochure

EN PDF 807 KB



### S8VK-S/S8FS-G Brochure

EN PDF 6.93 MB



### S8VK-T Switch Mode Power Supply Datasheet

EN PDF 4.07 MB

#### TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 12 May, 2023. Click here for [terms of use](#).

**OMRON**

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU