

Thrust ball bearings, single direction

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Minimum load factor A	Speed ratings		Mass	Designation
d	D	H	dynamic	static			Reference speed	Limiting speed		
mm			kN		kN	-	r/min		kg	-
45	65	14	26,5	69,5	2,55	0,025	4500	6300	0,15	51109

