



### Carrier Marking System, laser

• Helafix HC Carriers

#### Features and Benefits

The versatile Helafix HC and HCR character carriers are suitable for temporary or permanent marking. They are fixed in place using series T18 cable ties, screws or rivets. They are also easy to attach for temporary marking. Material and profile reliably protect the inserted label against damp, dirt, damage and UV radiation.

Helafix HC is supplied as cut lengths in bags, pre-cut and pre-punched. Helafix HCR is supplied in reel format and can be cut to size with the appropriate HCT tools.

We recommend HFX labels printed on an office laser printer using our Tagprint Pro labelling software.

#### Application

Marking of cable looms, cables, pipes, transport systems, valves, sensors, for inventory marking on machines or other parts.



Multi-purpose identification potential: Helafix HC and HCR.

Material Data	
Material	<b>Polyethylene, UV Resistant (PEUV)</b>
Colour	<b>Transparent (CL)</b>
Operating Temperature	<b>-60 °C to +65 °C</b>
Flammability	<b>UL94 HB</b>
Chem. Material Properties	<b>Excellent resistance to UV light, oils, water and a variety of solvents.</b>



Technical Table

Article-No.	Type	Length (L)	Height (H)	Recommended Labels	Pack Cont.	Reel Length	Application Tool
<b>Helafix HC</b>							
525-07173	<b>HC06-17</b>	17.5	7.00	-	50	-	-
525-07353	<b>HC06-35</b>	35.0	7.00	-	50	-	-
525-10173	<b>HC09-17</b>	17.5	10.00	HFX9-17P	50	-	-
525-10353	<b>HC09-35</b>	35.0	10.00	HFX9-35P	50	-	-
525-10523	<b>HC09-52</b>	52.0	10.00	HFX9-52P	50	-	-
525-13173	<b>HC12-17</b>	17.5	13.00	-	50	-	-
525-13353	<b>HC12-35</b>	35.0	13.00	HFX12-35P	50	-	-
525-13523	<b>HC12-52</b>	52.0	13.00	HFX12-52P	50	-	-
525-13703	<b>HC12-70</b>	70.0	13.00	-	50	-	-
525-19353	<b>HC 18-35</b>	35.0	19.00	-	50	-	-
525-19523	<b>HC 18-52</b>	52.0	19.00	-	50	-	-
525-19703	<b>HC 18-70</b>	70.0	19.00	-	50	-	-
525-25523	<b>HC 24-52</b>	52.0	25.00	-	50	-	-
525-25703	<b>HC 24-70</b>	70.0	25.00	-	50	-	-
<b>Helafix HCR</b>							
525-07003	<b>HCR 06</b>	-	7.00	-	25	25.0 m	-
525-10003	<b>HCR 09</b>	-	10.00	HFX9	25	25.0 m	HCT1
525-13003	<b>HCR 12</b>	-	13.00	HFX12	25	25.0 m	HCT2
525-19003	<b>HCR 18</b>	-	19.00	-	-	25.0 m	-
525-25003	<b>HCR 24</b>	-	25.00	-	-	25.0 m	-

All dimensions in mm. Subject to technical changes.

Technical Table

Article-No.	Type	For Carrier Width	For Size	Ø D
<b>Helafix HCT tang</b>				
525-00010	<b>HCT1</b>	10.00	HCR09	2.5
525-00013	<b>HCT2</b>	13.00	HCR12	2.5

All dimensions in mm. Subject to technical changes.

**We recommend as suitable labels Helafix HFX, see page 514.**

