


	1	2	3	4	5	6	7																																																														
A	 <p>Order Code AMET - XX - RS - 45 1</p> <p>1 No. of contacts 09,15,25,37</p> <p>Black anodized version on request</p> <p>09-poles only with one knurledge screw available</p> <p>Material Zinc die-cast</p> <p>Delivery includes 2 half-sheets 2 knurledge screws 2 screws 8 half shells of strain relief</p> <p>SPECIFICATION MATERIAL Features</p> <p>Material and finish Zinc-die-cast,nickel plated</p> <p>Temperature range -40° to +120°</p> <p>Cable diameter 4.0-13.0mm</p> <p>Attenuation factor >40 dB between 30Mhz and 1Ghz</p> <p>Requirements VDE 0871,FCC 20780, 89/336/EU</p>							A																																																													
B																																																																					
C																																																																					
D																																																																					
E																																																																					
F																																																																					
G				<table border="1"> <thead> <tr> <th>Modification</th> <th>Date</th> <th>Name</th> <th></th> <th>Date</th> <th>Name</th> <th>Title</th> </tr> </thead> <tbody> <tr> <td></td> <td></td> <td></td> <td>Drawn</td> <td>20.12.04</td> <td>Ken</td> <td rowspan="2">AMET-XX-RS-45</td> </tr> <tr> <td></td> <td></td> <td></td> <td>Approved</td> <td>02.07.07</td> <td>W.Hellwig</td> </tr> </tbody> </table>	Modification	Date	Name		Date	Name	Title				Drawn	20.12.04	Ken	AMET-XX-RS-45				Approved	02.07.07	W.Hellwig	G																																												
Modification	Date	Name		Date	Name	Title																																																															
			Drawn	20.12.04	Ken	AMET-XX-RS-45																																																															
			Approved	02.07.07	W.Hellwig																																																																
H	<table border="1"> <thead> <tr> <th colspan="8">Dimensions</th> </tr> <tr> <th>No.of contacts</th> <th>A1</th> <th>A</th> <th>B</th> <th>C</th> <th>D</th> <th>E</th> <th>F</th> </tr> </thead> <tbody> <tr> <td>09</td> <td>12.7</td> <td>---</td> <td>31.0</td> <td>19.3</td> <td>29.8</td> <td>31.2</td> <td>36.2</td> </tr> <tr> <td>15</td> <td>---</td> <td>33.3</td> <td>39.5</td> <td>20.7</td> <td>29.8</td> <td>35.2</td> <td>42.2</td> </tr> <tr> <td>25</td> <td>---</td> <td>47.0</td> <td>53.2</td> <td>20.8</td> <td>29.8</td> <td>35.2</td> <td>42.2</td> </tr> <tr> <td>37</td> <td>---</td> <td>63.5</td> <td>69.7</td> <td>20.8</td> <td>29.8</td> <td>35.2</td> <td>42.2</td> </tr> <tr> <td>A</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>			Dimensions								No.of contacts	A1	A	B	C	D	E	F	09	12.7	---	31.0	19.3	29.8	31.2	36.2	15	---	33.3	39.5	20.7	29.8	35.2	42.2	25	---	47.0	53.2	20.8	29.8	35.2	42.2	37	---	63.5	69.7	20.8	29.8	35.2	42.2	A								<table border="1"> <tr> <td rowspan="3" style="text-align: center; vertical-align: middle;">ASSMANN WSW Components</td> <td>Drawing-No.</td> <td>Sheet</td> </tr> <tr> <td>ASS 0411A CO</td> <td>rev01</td> </tr> <tr> <td>Replace</td> <td>Sheet</td> </tr> </table>		ASSMANN WSW Components	Drawing-No.	Sheet	ASS 0411A CO	rev01	Replace	Sheet	H
Dimensions																																																																					
No.of contacts	A1	A	B	C	D	E	F																																																														
09	12.7	---	31.0	19.3	29.8	31.2	36.2																																																														
15	---	33.3	39.5	20.7	29.8	35.2	42.2																																																														
25	---	47.0	53.2	20.8	29.8	35.2	42.2																																																														
37	---	63.5	69.7	20.8	29.8	35.2	42.2																																																														
A																																																																					
ASSMANN WSW Components	Drawing-No.	Sheet																																																																			
	ASS 0411A CO	rev01																																																																			
	Replace	Sheet																																																																			
	1	2	3	4	5	6	7	P62																																																													