



HSS-G DIN 338 Jobber Bit Sets

Selling Proposition

- Precision ground twist drill for rapid drilling, long life and excellent concentricity.
- Manufactured from High Speed Steel to DIN338.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Finish - bright.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm

Applications

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

Warranty Specifications

- 12 months warranty

Specifications



Cat. No. & Product Description	Description	Diameters mm	Pack Quantity	M.O.Q.	
DT5923	HSS-G DIN 338 Jobber Metal Drill Bit Sets	19 piece set in metal cassette	1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5	19	1
DT5922	HSS-G DIN 338 Jobber Metal Drill Bit Sets	13 piece set in plastic casset	1.5, 2, 2.5, 3.2, 3, 3.5, 4, 4	13	1
DT5921	HSS-G DIN 338 Jobber Metal Drill Bit Sets	10 piece set in plastic casset	1, 2, 3, 4, 5, 6, 7, 8, 9, 10	10	1
DT5929	HSS-G DIN 338 Jobber Metal Drill Bit Sets	29 piece set	1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.	29	1