

规格书编号

SPEC NO:

产品规格书


SPECIFICATION

CUSTOMER 客户: _____
PRODUCT 产品: _____ SAW FILTER _____
MODEL NO 型号: _____ HDF711N4-S21 _____
PREPARED 编制: _____ CHECKED 审核: _____
APPROVED 批准: _____ DATE 日期: _____ 2013-3-18 _____

客户确认 CUSTOMER RECEIVED:		
审核 CHECKED	批准 APPROVED	日期 DATE

无锡市好达电子有限公司
Shoulder Electronics Limited

1. Package Dimension



I. Input
D. Output
Other Ground

2. Performance


2.1 Maximum Rating

Operation Temperature Range	-40°C to +70°C
Storage Temperature Range	-45°C to +85°C
RF Power	10dBm


2.2 Electronic Characteristics

	Unit	Minimum	Typical	Maximum
Center Frequency	MHz	710.6	711	711.4
Insertion Loss	dB	-	10	13
3dB Bandwidth	MHz	2	2.5	-
Attenuation				
0.3 MHz ~ Fc-3 MHz	dB	30	35	-
Fc+3 MHz ~ 1000MHz	dB	30	35	-
Input/Output Impedance	Ohms		50	

2.3 Frequency Characteristics



3. Test Circuit



OR

