

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201090006](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Ultra-Lock (M12) Ethernet Receptacle D-Code, Female (Straight) to RJ-45 Male Plug, 4 Poles, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Receptacles
 Series [120109](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad Industrial Ethernet Solutions](#)
 Product Name RJ45, Ultra-Lock (M12)
 Type Double Ended
 UPC 78172509482

Physical

Coupling Type External Thread
 Gender Female-Male
 Keyway D-coded
 Length 1.0m
 Material - Component Nickel-plated Brass
 Mounting Thread Size M12
 Orientation Straight
 Panel Mount N/A
 Poles 5
 Temperature Range - Operating N/A
 Wire Size AWG N/A
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum N/A

Material Info

Engineering Number ERWPAU7005M010

Reference - Drawing Numbers

Sales Drawing SD-120109-014



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120109 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120109-0006](#)