


8713 Max. 7,5 W

AC/DC ADAPTERS – REGULATED

Adjustable output voltage
Justerbar utgangsspenning

- Plug-in unit
- Stepless adjustable output voltage 5-15 VDC
- Also available with fixed output voltage - see table
- Thermal fuse in transformer and thermal protection in the regulator
- Exchangeable output plugs
- Approvals:
 - Complies w. medical std EN 60601 (on request)
- Plugg-inn enhet
- Trinnløs justerbar utgangsspenning fra 5-15 VDC
- Finnes også med faste utgangsspenninger - se tabell
- Termosikring i transformator og termisk beskyttelse i regulator
- Utskiftbare plugger
- Godkjenninger:
 - Tilfredsst. medisinsk std EN 60601 (på forespørsel)



Technical specifications


Input voltage:
Output voltage:
Max. output power:
Ripple:
Insulation class:
Electrical safety standard:
EMC standards
• Emission:
• Immunity:
Output terminals
Cord with/without plug:
Dimensions excl. plug (LxWxH):
Weight:

Tekniske data

Inngangsspenning:
Utgangsspenning:
Maks. utgangseffekt:
Rippel:
Isolasjonsklasse:
Elektrisk sikkerhetsstandard:
EMC standarder
• Emisjon:
• Immunitet:
Utgangsterminaler
Sek. ledning med/uten plugg:
Mål uten plugg (LxBxH):
Vekt:

230 VAC +6/-10%, 50/60Hz
5-15 VDC
7,5 W
< 30 mV p-p
II
EN 60065, EN 60950
EN 61000-6-3
EN 61000-6-1
Accessories /Tilbehør
100 x 51 x 63 mm
450 g

Adjustable / Justerbar -



Fixed output voltages
Faste utgangsspenninger

Voltage version (VDC) Spenningsversjoner (VDC)	Nominal load (mA) Merkelast (mA)
5	800
6	800
7,5	700
9	700
12	580
15	500
18	440
24	330