


hand slide valve VBOH-32-G18

Part number: 1558073

FESTO



Data sheet

Feature	Value
Valve function	3/2 bistable
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Type of actuation	manual
Mounting type	Line installation Threaded
Standard nominal flow rate	777 l/min
Nominal size	5.7 mm
Operating pressure	-0.95 ... 12 bar
Ambient temperature	-10 ... 80 °C
Material housing	Wrought Aluminium alloy Anodised
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Grid dimension	24 mm
Sealing principle	soft
Assembly position	Any
Design structure	Sleeve slide
Type of piloting	direct
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-10 ... 80 °C
Actuating force	17 N
Product weight	17 g
Material of threaded plug	Wrought Aluminium alloy Anodised
Materials note	Conforms to RoHS
Material seals	NBR